






[illegible]

 NYLON, UL94V-2, NATURAL.

2. DIMENSIONS IN BRACKETS ARE IN INCHES.


3. FEMALE CONTACTS MUST BE INSERTED SO THAT THE TOP OF THE WIRE AND INSULATION CRIMPS ARE FACING THE CIRCUIT NUMBER OF THE POSITION INTO WHICH IT IS BEING INSERTED OR 180° FROM THE CIRCUIT NUMBER FOR THAT POSITION.



SCALE 4:1

4032.2	24	46.2[1.82]	51.7[2.04]	2-106527-4
3717.6	22	42[1.65]	47.5[1.87]	2-106527-2
3403.1	20	37.8[1.49]	43.3[1.7]	2-106527-0
3088.6	18	33.6[1.32]	39.1[1.54]	1-106527-8
2774	16	29.4[1.16]	34.9[1.37]	1-106527-6
2459.5	14	25.2[0.99]	30.7[1.21]	1-106527-4
2145	12	21[0.83]	26.5[1.04]	1-106527-2
1830.5	10	16.8[0.66]	22.3[0.88]	1-106527-0
1515.9	8	12.6[0.5]	18.1[0.71]	106527-8
1201.4	6	8.4[0.33]	13.9[0.55]	106527-6
886.9	4	4.2[0.17]	9.7[0.38]	106527-4
575.1	2	0[0]	5.5[0.22]	106527-2
VOLUME mm ³	NO OF POSITIONS	B	A±0.2[.01]	PART NUMBER

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWG. K. WHITAKER 27JUN2007 CHK. C. CASH 27JUN2007 APVD. C. CASH 27JUN2007		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME AMP-DUAC(TM) RECEPTACLE HOUSING, 2 TO 24 POSITION,	
		0 PLC ±0.21 (0.1) 1 PLC ±0.21 (0.1) 2 PLC ±0.13 (0.005) 3 PLC ±- 4 PLC ±- ANGLES ±90° 30'		PRODUCT SPEC - APPLICATION SPEC -	
MATERIAL FINISH		WEIGHT -		SIZE CASE CODE DRAWING NO A100779C=106527	
		CUSTOMER DRAWING		SCALE 4:1 SHEET 1 OF REV F	