International
IOR Rectifier

StrongIRFET™
IRFB7530PbF
IRFS7530PbF
IRFSL7530PbF

HEXFET® Power MOSFET

Application
- Brushed Motor drive applications
- BLDC Motor drive applications
- Battery powered circuits
- Half-bridge and full-bridge topologies
- Synchronous rectifier applications
- Resonant mode power supplies
- OR-ing and redundant power switches
- DC/DC and AC/DC converters
- DC/AC Inverters



V_{DSS}	60V
$R_{DS(on)}$ typ.	1.65mΩ
max	2.00mΩ
$I_{D\ (Silicon\ Limited)}$	295A①
$I_{D\ (Package\ Limited)}$	195A

Benefits
- Improved Gate, Avalanche and Dynamic dV/dt Ruggedness
- Fully Characterized Capacitance and Avalanche SOA
- Enhanced body diode dV/dt and dI/dt Capability
- Lead-Free, RoHS Compliant

TO-220AB
IRFB7530PbF



D^2Pak
IRFS7530PbF



TO-262
IRFSL7530PbF

G	D	S
Gate	Drain	Source

Base part number	Package Type	Standard Pack		Orderable Part Number
		Form	Quantity	
IRFB7530PbF	TO-220	Tube	50	IRFB7530PbF
IRFSL7530PbF	TO-262	Tube	50	IRFSL7530PbF
IRFS7530PbF	D^2-Pak	Tube	50	IRFS7530PbF
		Tape and Reel Left	800	IRFS7530TRLPbF



Fig 1. Typical On-Resistance vs. Gate Voltage



Fig 2. Maximum Drain Current vs. Case Temperature

 © 2014 International Rectifier

Absolute Maximum Rating

Symbol	Parameter	Max.	Units
I_D @ T_C = 25°C	Continuous Drain Current, V_{GS} @ 10V (Silicon Limited)	295①	A
I_D @ T_C = 100°C	Continuous Drain Current, V_{GS} @ 10V (Silicon Limited)	208①	
I_D @ T_C = 25°C	Continuous Drain Current, V_{GS} @ 10V (Wire Bond Limited)	195	
I_{DM}	Pulsed Drain Current ②	760	
P_D @T_C = 25°C	Maximum Power Dissipation	375	W
	Linear Derating Factor	2.5	W/°C
V_{GS}	Gate-to-Source Voltage	± 20	V
T_J T_{STG}	Operating Junction and Storage Temperature Range	-55 to + 175	°C
	Soldering Temperature, for 10 seconds (1.6mm from case)	300	
	Mounting Torque, 6-32 or M3 Screw	10 lbf·in (1.1 N·m)	

Avalanche Characteristics

$E_{AS\ (Thermally\ limited)}$	Single Pulse Avalanche Energy ③	524	mJ
$E_{AS\ (Thermally\ limited)}$	Single Pulse Avalanche Energy ⑩	1025	
I_{AR}	Avalanche Current ②	See Fig 15, 16, 23a, 23b	A
E_{AR}	Repetitive Avalanche Energy ②		mJ

Thermal Resistance

Symbol	Parameter	Typ.	Max.	Units
$R_{\theta JC}$	Junction-to-Case ⑧	–––	0.40	°C/W
$R_{\theta CS}$	Case-to-Sink, Flat Greased Surface	0.50	–––	
$R_{\theta JA}$	Junction-to-Ambient (TO-220)	–––	62	
$R_{\theta JA}$	Junction-to-Ambient (PCB Mount) (D^2-Pak)⑨	–––	40	

Static @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
$V_{(BR)DSS}$	Drain-to-Source Breakdown Voltage	60	–––	–––	V	V_{GS} = 0V, I_D = 250µA
$\Delta V_{(BR)DSS}/\Delta T_J$	Breakdown Voltage Temp. Coefficient	–––	47	–––	mV/°C	Reference to 25°C, I_D = 1mA ②
$R_{DS(on)}$	Static Drain-to-Source On-Resistance	–––	1.65	2.00	mΩ	V_{GS} = 10V, I_D = 100A
		–––	2.10	–––		V_{GS} = 6.0V, I_D = 50A
$V_{GS(th)}$	Gate Threshold Voltage	2.1	–––	3.7	V	V_{DS} = V_{GS}, I_D = 250µA
I_{DSS}	Drain-to-Source Leakage Current	–––	–––	1.0	µA	V_{DS} =60 V, V_{GS} = 0V
		–––	–––	150		V_{DS} =60V,V_{GS} = 0V,T_J =125°C
I_{GSS}	Gate-to-Source Forward Leakage	–––	–––	100	nA	V_{GS} = 20V
	Gate-to-Source Reverse Leakage	–––	–––	-100		V_{GS} = -20V
R_G	Gate Resistance	–––	2.1	–––	Ω	

Notes:

① Calculated continuous current based on maximum allowable junction temperature. Bond wire current limit is 195A by source bonding technology. Note that current limitations arising from heating of the device leads may occur with some lead mounting arrangements. (Refer to AN-1140)

② Repetitive rating; pulse width limited by max. junction temperature.

③ Limited by T_{Jmax}, starting T_J = 25°C, L = 105µH, R_G = 50Ω, I_{AS} = 100A, V_{GS} =10V.

④ $I_{SD} \le$ 100A, di/dt ≤ 1338A/µs, $V_{DD} \le V_{(BR)DSS}$, $T_J \le$ 175°C.

⑤ Pulse width ≤ 400µs; duty cycle ≤ 2%.

⑥ C_{oss} eff. (TR) is a fixed capacitance that gives the same charging time as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑦ C_{oss} eff. (ER) is a fixed capacitance that gives the same energy as C_{oss} while V_{DS} is rising from 0 to 80% V_{DSS}.

⑧ R_θ is measured at T_J approximately 90°C.

⑨ When mounted on 1" square PCB (FR-4 or G-10 Material). For recommended footprint and soldering techniques refer to application note #AN-994.: http://www.irf.com/technical-info/appnotes/an-994.pdf

⑩ Limited by T_{Jmax}, starting T_J = 25°C, L = 1mH, R_G = 50Ω, I_{AS} = 45A, V_{GS} =10V.

 © 2014 International Rectifier

Dynamic Electrical Characteristics @ T_J = 25°C (unless otherwise specified)

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
gfs	Forward Transconductance	242	—	—	S	V_{DS} = 10V, I_D =100A
Q_g	Total Gate Charge	—	274	411	nC	I_D = 100A
Q_{gs}	Gate-to-Source Charge	—	64	—		V_{DS} = 30V
Q_{gd}	Gate-to-Drain Charge	—	83	—		V_{GS} = 10V
Q_{sync}	Total Gate Charge Sync. (Qg– Qgd)	—	191	—		
$t_{d(on)}$	Turn-On Delay Time	—	52	—	ns	V_{DD} = 30V
t_r	Rise Time	—	141	—		I_D = 100A
$t_{d(off)}$	Turn-Off Delay Time	—	172	—		R_G= 2.7Ω
t_f	Fall Time	—	104	—		V_{GS} = 10V⑤
C_{iss}	Input Capacitance	—	13703	—	pF	V_{GS} = 0V
C_{oss}	Output Capacitance	—	1266	—		V_{DS} = 25V
C_{rss}	Reverse Transfer Capacitance	—	806	—		f = 1.0MHz, See Fig.7
$C_{oss\ eff.(ER)}$	Effective Output Capacitance (Energy Related)	—	1267	—		V_{GS} = 0V, VDS = 0V to 48V⑦
$C_{oss\ eff.(TR)}$	Output Capacitance (Time Related)	—	1630	—		V_{GS} = 0V, VDS = 0V to 48V⑥

Diode Characteristics

Symbol	Parameter	Min.	Typ.	Max.	Units	Conditions
I_S	Continuous Source Current (Body Diode)	—	—	295①	A	MOSFET symbol showing the integral reverse p-n junction diode. 
I_{SM}	Pulsed Source Current (Body Diode) ②	—	—	760		
V_{SD}	Diode Forward Voltage	—	—	1.2	V	T_J = 25°C,I_S = 100A,V_{GS} = 0V ⑤
dv/dt	Peak Diode Recovery dv/dt④	—	8.1	—	V/ns	T_J = 175°C,I_S =100A,V_{DS} = 60V⑤
t_{rr}	Reverse Recovery Time	—	51	—	ns	T_J = 25°C V_{DD} = 51V
		—	54	—		T_J = 125°C I_F = 100A,
Q_{rr}	Reverse Recovery Charge	—	86	—	nC	T_J = 25°C di/dt = 100A/µs ⑤
		—	102	—		T_J = 125°C
I_{RRM}	Reverse Recovery Current	—	2.9	—	A	T_J = 25°C

 © 2014 International Rectifier



Fig 3. Typical Output Characteristics



Fig 4. Typical Output Characteristics



Fig 5. Typical Transfer Characteristics



Fig 6. Normalized On-Resistance vs. Temperature



Fig 7. Typical Capacitance vs. Drain-to-Source Voltage



Fig 8. Typical Gate Charge vs. Gate-to-Source Voltage

 © 2014 International Rectifier



Fig 9. Typical Source-Drain Diode Forward Voltage



Fig 10. Maximum Safe Operating Area



Fig 11. Drain-to-Source Breakdown Voltage



Fig 12. Typical C_{oss} Stored Energy



Fig 13. Typical On-Resistance vs. Drain Current

 © 2014 International Rectifier



Fig 14. Maximum Effective Transient Thermal Impedance, Junction-to-Case



Fig 15. Avalanche Current vs. Pulse Width



Fig 16. Maximum Avalanche Energy vs. Temperature

Notes on Repetitive Avalanche Curves , Figures 15, 16:
(For further info, see AN-1005 at www.irf.com)

1.Avalanche failures assumption:
Purely a thermal phenomenon and failure occurs at a temperature far in excess of T_{jmax}. This is validated for every part type.

2. Safe operation in Avalanche is allowed as long asT_{jmax} is not exceeded.

3. Equation below based on circuit and waveforms shown in Figures 23a, 23b.

4. $P_{D\ (ave)}$ = Average power dissipation per single avalanche pulse.

5. BV = Rated breakdown voltage (1.3 factor accounts for voltage increase during avalanche).

6. I_{av} = Allowable avalanche current.

7. ΔT = Allowable rise in junction temperature, not to exceed T_{jmax} (assumed as 25°C in Figure 15, 16).

t_{av} = Average time in avalanche.

D = Duty cycle in avalanche = tav ·f

$Z_{thJC}(D, t_{av})$ = Transient thermal resistance, see Figures 14)

PD (ave) = 1/2 (1.3·BV·I_{av}) = $\Delta T/ Z_{thJC}$

$I_{av} = 2\Delta T/ [1.3 \cdot BV \cdot Z_{th}]$

$E_{AS\ (AR)} = P_{D\ (ave)} \cdot t_{av}$

 © 2014 International Rectifier



Fig 17. Threshold Voltage vs. Temperature



Fig 18. Typical Recovery Current vs. dif/dt



Fig 19. Typical Recovery Current vs. dif/dt



Fig 20. Typical Stored Charge vs. dif/dt



Fig 21. Typical Stored Charge vs. dif/dt

 © 2014 International Rectifier



Fig 22. Peak Diode Recovery dv/dt Test Circuit for N-Channel HEXFET® Power MOSFETs



Fig 23a. Unclamped Inductive Test Circuit



Fig 23b. Unclamped Inductive Waveforms



Fig 24a. Switching Time Test Circuit



Fig 24b. Switching Time Waveforms



Fig 25a. Gate Charge Test Circuit



Fig 25b. Gate Charge Waveform

 © 2014 International Rectifier

TO-220AB Package Outline (Dimensions are shown in millimeters (inches))



NOTES:

1.– DIMENSIONING AND TOLERANCING AS PER ASME Y14.5 M– 1994.
2.– DIMENSIONS ARE SHOWN IN INCHES [MILLIMETERS].
3.– LEAD DIMENSION AND FINISH UNCONTROLLED IN L1.
4.– DIMENSION D, D1 & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED .005" (0.127) PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTERMOST EXTREMES OF THE PLASTIC BODY.
5.– DIMENSION b1, b3 & c1 APPLY TO BASE METAL ONLY.
6.– CONTROLLING DIMENSION : INCHES.
7.– THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSIONS E,H1,D2 & E1
8.– DIMENSION E2 X H1 DEFINE A ZONE WHERE STAMPING AND SINGULATION IRREGULARITIES ARE ALLOWED.
9.– OUTLINE CONFORMS TO JEDEC TO-220, EXCEPT A2 (max.) AND D2 (min.) WHERE DIMENSIONS ARE DERIVED FROM THE ACTUAL PACKAGE OUTLINE.

SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	3.56	4.83	.140	.190	
A1	1.14	1.40	.045	.055	
A2	2.03	2.92	.080	.115	
b	0.38	1.01	.015	.040	
b1	0.38	0.97	.015	.038	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.36	0.61	.014	.024	
c1	0.36	0.56	.014	.022	5
D	14.22	16.51	.560	.650	4
D1	8.38	9.02	.330	.355	
D2	11.68	12.88	.460	.507	7
E	9.65	10.67	.380	.420	4,7
E1	6.86	8.89	.270	.350	7
E2	–	0.76	–	.030	8
e	2.54 BSC		.100 BSC		
e1	5.08 BSC		.200 BSC		
H1	5.84	6.86	.230	.270	7,8
L	12.70	14.73	.500	.580	
L1	3.56	4.06	.140	.160	3
øP	3.54	4.08	.139	.161	
Q	2.54	3.42	.100	.135	

LEAD ASSIGNMENTS

HEXFET
1.– GATE
2.– DRAIN
3.– SOURCE

IGBTs, CoPACK
1.– GATE
2.– COLLECTOR
3.– EMITTER

DIODES
1.– ANODE
2.– CATHODE
3.– ANODE

TO-220AB Part Marking Information

EXAMPLE: THIS IS AN IRF1010
LOT CODE 1789
ASSEMBLED ON WW 19, 2000
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position
indicates "Lead - Free"



TO-220AB packages are not recommended for Surface Mount Application.

Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

 © 2014 International Rectifier

TO-262 Package Outline (Dimensions are shown in millimeters (inches)



SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	4.06	4.83	.160	.190	
A1	2.03	3.02	.080	.119	
b	0.51	0.99	.020	.039	
b1	0.51	0.89	.020	.035	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.38	0.74	.015	.029	
c1	0.38	0.58	.015	.023	5
c2	1.14	1.65	.045	.065	
D	8.38	9.65	.330	.380	3
D1	6.86	–	.270	–	4
E	9.65	10.67	.380	.420	3,4
E1	6.22	–	.245		4
e	2.54 BSC		.100 BSC		
L	13.46	14.10	.530	.555	
L1	–	1.65	–	.065	4
L2	3.56	3.71	.140	.146	

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M–1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1 AND c1 APPLY TO BASE METAL ONLY.
6. CONTROLLING DIMENSION: INCH.
7. – OUTLINE CONFORM TO JEDEC TO-262 EXCEPT A1(max.), b(min.) AND D1(min.) WHERE DIMENSIONS DERIVED THE ACTUAL PACKAGE OUTLINE.

LEAD ASSIGNMENTS

IGBTs, CoPACK

1.– GATE
2.– COLLECTOR
3.– EMITTER
4.– COLLECTOR

HEXFET	DIODES
1.– GATE	1.– ANODE (TWO DIE) / OPEN (ONE DIE)
2.– DRAIN	2, 4.– CATHODE
3.– SOURCE	3.– ANODE
4.– DRAIN	

TO-262 Part Marking Information

EXAMPLE: THIS IS AN IRL3103L
LOT CODE 1789
ASSEMBLED ON WW 19, 1997
IN THE ASSEMBLY LINE "C"

Note: "P" in assembly line position indicates "Lead – Free"



OR



Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

 © 2014 International Rectifier

D²Pak (TO-263AB) Package Outline (Dimensions are shown in millimeters (inches))



SYMBOL	DIMENSIONS				NOTES
	MILLIMETERS		INCHES		
	MIN.	MAX.	MIN.	MAX.	
A	4.06	4.83	.160	.190	
A1	0.00	0.254	.000	.010	
b	0.51	0.99	.020	.039	
b1	0.51	0.89	.020	.035	5
b2	1.14	1.78	.045	.070	
b3	1.14	1.73	.045	.068	5
c	0.38	0.74	.015	.029	
c1	0.38	0.58	.015	.023	5
c2	1.14	1.65	.045	.065	
D	8.38	9.65	.330	.380	3
D1	6.86	–	.270	–	4
E	9.65	10.67	.380	.420	3,4
E1	6.22	–	.245	–	4
e	2.54 BSC		.100 BSC		
H	14.61	15.88	.575	.625	
L	1.78	2.79	.070	.110	
L1	–	1.68	–	.066	4
L2	–	1.78	–	.070	
L3	0.25 BSC		.010 BSC		

NOTES:

1. DIMENSIONING AND TOLERANCING PER ASME Y14.5M–1994
2. DIMENSIONS ARE SHOWN IN MILLIMETERS [INCHES].
3. DIMENSION D & E DO NOT INCLUDE MOLD FLASH. MOLD FLASH SHALL NOT EXCEED 0.127 [.005"] PER SIDE. THESE DIMENSIONS ARE MEASURED AT THE OUTMOST EXTREMES OF THE PLASTIC BODY AT DATUM H.
4. THERMAL PAD CONTOUR OPTIONAL WITHIN DIMENSION E, L1, D1 & E1.
5. DIMENSION b1, b3 AND c1 APPLY TO BASE METAL ONLY.
6. DATUM A & B TO BE DETERMINED AT DATUM PLANE H.
7. CONTROLLING DIMENSION: INCH.
8. OUTLINE CONFORMS TO JEDEC OUTLINE TO-263AB.

LEAD ASSIGNMENTS

DIODES

1.– ANODE (TWO DIE) / OPEN (ONE DIE)
2, 4.– CATHODE
3.– ANODE

HEXFET

1.– GATE
2, 4.– DRAIN
3.– SOURCE

IGBTs, CoPACK

1.– GATE
2, 4.– COLLECTOR
3.– EMITTER

D²Pak (TO-263AB) Part Marking Information

EXAMPLE: THIS IS AN IRF530S WITH LOT CODE 8024
ASSEMBLED ON WW 02, 2000
IN THE ASSEMBLY LINE "L"

Note: "P" in assembly line position indicates "Lead – Free"



OR



Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

 © 2014 International Rectifier

D²Pak (TO-263AB) Tape & Reel Information (Dimensions are shown in millimeters (inches))



NOTES :
1. COMFORMS TO EIA-418.
2. CONTROLLING DIMENSION: MILLIMETER.
3. DIMENSION MEASURED @ HUB.
4. INCLUDES FLANGE DISTORTION @ OUTER EDGE.

Note: For the most current drawing please refer to IR website at http://www.irf.com/package/

 © 2014 International Rectifier

Qualification Information†

Qualification Level	Industrial (per JEDEC JESD47F) ††	
Moisture Sensitivity Level	TO-220	N/A
	D^2Pak	MSL1
	TO-262	N/A
RoHS Compliant	Yes	

† Qualification standards can be found at International Rectifier's web site: http://www.irf.com/product-info/reliability/

†† Applicable version of JEDEC standard at the time of product release.

Revision History

Date	Comments
11/7/2014	• Updated $E_{AS\ (L\ =1mH)}$ = 1025mJ on page 2 • Updated note 10 "Limited by T_{Jmax}, starting T_J = 25°C, L = 1mH, R_G = 50Ω, I_{AS} = 45A, V_{GS} =10V". on page 2 • Updated package outline on page 9,10,11.

International
IOR Rectifier

IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA
To contact International Rectifier, please visit http://www.irf.com/whoto-call/

 © 2014 International Rectifier