



## TECHNICAL DATA SHEET

### RS 251-3794 Lubricant

RS 251-3794 is suitable for regular use on mechanical assemblies for lubricating sprocket wheels, ball races, gears and axles, for example. It may also be used for cleaning and lubricating gold contacts on edge connectors and for cleaning and protecting relays, particularly from silicone contamination.

- A high performance lubricant for many regular maintenance jobs
- Fast evaporating solvent allowing a speedy return to normal service
- Extremely long life with excellent wear characteristics; prevents dust build up over time
- Exhibits excellent electrical and thermal resistance

**Approvals**                      **RoHS-2 Compliant (2011/65/EU):**                      **Yes**

#### Typical Properties

Colour	Clear
Density (g/ml)	0.65
Flash Point (COC ASTM D 92 (°C))	-48
UV Trace	No
Temperature Range (°C)	-40 to +180
Evaporation Weight Loss (% 7 days @ 125°C)	0.20

**Packaging**                      **Order Code**

200ml Aerosol                      ULL200D

#### **Directions for Use**

Disconnect all apparatus from the power supply. Spray onto on the area to be cleaned and lubricated. If heavy dust deposits are evident spray with an airduster prior to treating with RS 251-3794. Ensure that all the solvent has evaporated before reconnecting to the power supply. Test suitability when using on any sensitive plastics.