


MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
4	BD	35				D	REDRAWN PER EC 0020-774-94	09/15/94	AF



- THIS CONNECTOR ACCEPTS FIVE (5) SIZE 16 MULTIMATE SOCKET CONTACTS. MAXIMUM WIRE INSULATION DIAMETER = .135
 - THIS CONNECTOR MATES WITH AMP P/N 208720-1.
- 3 AMP P/N & DATE CODE INK STAMPED ON ANY OF THE FOUR SIDE SURFACES.
- 4 THERMOPLASTIC, BLACK.
- 5 ZINC PER QQ-Z-363.
- 6 NICKEL PER QQ-N-290 OVER COPPER PER MIL-C-14550.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

					PART NO	
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± 0.13 [.005] 3 PLC DEC ± - ANGLES ± - MATERIAL SOCKET HOUSING:  RECEPTACLE SHELL:  FINISH RECEPTACLE SHELL: 	DR 3/19/82 T. SMITH		AMP AMP Incorporated Harrisburg, PA 17105-3608			
	CHK 9/26/94 B. LENKER					
	APPD 9/29/94 A. FRANTUM		NAME RECEPTACLE ASSEMBLY, REVERSE SEX, SERIES I, 14-5, CMC			
	APPD 9/29/94 R. EASTON					
PRODUCT SPEC 108-10040						
APPLICATION SPEC -		SIZE 	CAGE CODE 00779	DRAWING NO C=208721		
WEIGHT -		SCALE 2:1			SHEET 1 OF 1	