



Real Time Clock Module with I²C-Bus

Real Time Clock Module with I²C-Bus



Package:

Technical drawing of the package showing top, side, and cross-section views. The top view shows a central rectangular area with a width of 5.0 ± 0.2 mm and a height of 3.2 ± 0.2 mm. There are four mounting tabs on the top and bottom edges, each with a width of 1.0 mm and a height of 0.4 mm. The side view shows a height of 0.35 mm. The cross-section view shows a maximum height of 1.2 mm and a width of 0.6 mm.

Recommended Solder Pad:

Technical drawing of the recommended solder pad showing top and side views. The top view shows a central rectangular area with a width of 4.6 mm and a height of 2.2 mm. There are four mounting tabs on the top and bottom edges, each with a width of 1.0 mm and a height of 0.9 mm. The side view shows a height of 0.6 mm.

All dimensions in mm typical

All dimensions in mm typical

Option A: Temperature	Calibrated Time Deviation	
@ +25°C	± 0.26 s/day	± 3ppm
0°C to +50°C	± 0.35 s/day	± 4ppm
-10°C to +60°C	± 0.44 s/day	± 5ppm
-40°C to +85°C	± 0.52 s/day	± 6ppm
-40°C to +125°C	± 0.70 s/day	± 8ppm

Option B:	Default	
Temperature	Time Deviation	
@ +25°C	± 0.26 s/day	± 3ppm
0°C to +50°C	± 0.44 s/day	± 5ppm
-10°C to +60°C	± 0.87 s/day	±10ppm
-40°C to +85°C	± 2.17 s/day	±25ppm

The RV-3029-C2 is a Real-Time-Clock Module with embedded Crystal. This RTC has an I²C Bus (2-wire Serial-Interface) and offers temperature compensated time. The STC-Smart Temperature Compensation is calibrated in the factory and leads to a very high time-accuracy of ± 6 ppm from -40°C to +85°C and ± 8 ppm from -40°C to +125°C.

Beside standard RTC functions, it includes a Backup-Battery Input with internal switchover function, a programmable Trickle-charge circuitry, an integrated Temperature Sensor with digital-output and offers 8 Bytes RAM and 2 Bytes EEPROM for customer's application.

The calendar function tracks year and leap -year flags. The clock tracks second, minute and hour in 24-hour format. Programmable alarm setting and universal timer functions increase flexibility.

For pick-and-place equipment, the parts are available in 12 mm tape:

7" (178 mm) reel with 1'000 parts

13" (330 mm) reel with 5'000 parts

ELECTRICAL CHARACTERISTICS AT 25°C:

	Symbol	Condition	Min.	Typ.	Max	Unit
Supply voltage	V_{DD}	Time keeping	1.3		5.5	V
Supply voltage	V_{DD}	Temp. comp.	1.8		5.5	V
Current consumption	I_{DDO}	$V_{DD} = 3V$		800	1000	nA
CLKOUT frequency		Progr.	32.768/1024/32/1			Hz
Frequency Tolerance	$\Delta F/F$	@ 25°C		±10	±20	ppm
Freq.vs.Temp.	$\Delta F/F_{TOPR}$	$20 \leq T_0 \leq 30$	$-0.035 \text{ ppm}/^{\circ}\text{C}^2 (T - T_0)^2 \pm 10\%$			ppm
Aging first year	$\Delta F/F$	@ 25°C			± 3	ppm
Time accuracy Opt. A	$\Delta t/t$	@ 25°C			±0.26	s/day
		-40 to +85°C			±0.52	s/day
Time accuracy Opt. B	$\Delta t/t$	@ 25°C			±0.26	s/day
		-40 to +85°C			±2.17	s/day


ENVIRONMENTAL CHARACTERISTICS:

		Conditions	Max. Dev.
Storage temp. range		-55 to +125°C	
TA Operating temperature range		-40 to +85°C	
TB Extended oper. temp. range		-40 to +125°C	
Shock resistance	$\Delta F/F$	5000 g, 0.3 ms, 1/2 sine	± 5 ppm
Vibration resistance	$\Delta F/F$	20 g / 10–2000 Hz	± 5 ppm

PACKAGE, TERMINATIONS AND PROCESSING:

Package-Type	Termination	Processing
SON 10-pin	For SMD mounting Au plated pads	Reflow soldering 260°C/20 s max.

FREQUENCY TEMPERATURE CHARACTERISTICS:



PIN CONNECTIONS TOP VIEW:

Product Marking	Pin	Connection
	1	V_{DD} Power Supply Voltage
	2	CLKOUT Frequency Output
	3	N.C. not connected
	4	SCL Serial Clock Input
	5	SDA Serial Data
	6	V_{SS} Ground
	7	INT Interrupt Output
	8	V_{BACKUP} Backup Supply Voltage
	9	N.C. not connected
	10	CLKOE CLK Output Enable

All specifications subject to change without notice.



Micro Crystal AG
Mühlestrasse 14
CH-2540 Grenchen
Switzerland

Tel. +41 32 655 82 82
Fax +41 32 655 82 83
sales@microcrystal.com
www.microcrystal.com