


## DG M TNC 440 FM (952 308)


- Prewired complete unit consisting of a base part and plug-in protection modules
- High discharge capacity due to heavy-duty zinc oxide varistors / spark gaps
- High reliability due to "Thermo Dynamic Control" SPD monitoring device



Figure without obligation



Basic circuit diagram DG M TNC 440 FM



Dimension drawing DG M TNC 440 FM

Modular surge arrester for use in TN-C systems; with floating changeover contact.

Type	DG M TNC 440 FM
Part No.	952 308
SPD according to EN 61643-11 / IEC 61643-11	type 2 / class II
Nominal a.c. voltage ( $U_N$ )	400 / 690V (50 / 60 Hz)
Max. continuous operating a.c. voltage ( $U_C$ )	440 V (50 / 60 Hz)
Nominal discharge current (8/20 $\mu$ s) ( $I_n$ )	20 kA
Max. discharge current (8/20 $\mu$ s) ( $I_{max}$ )	40 kA
Voltage protection level ( $U_P$ )	$\leq 2$ kV
Voltage protection level at 5 kA ( $U_P$ )	$\leq 1.7$ kV
Response time ( $t_d$ )	$\leq 25$ ns
Max. mains-side overcurrent protection	125 A gG
Short-circuit withstand capability for max. mains-side overcurrent protection ( $I_{SCCR}$ )	25 kA <sub>rms</sub>
Temporary overvoltage (TOV) ( $U_T$ ) – Characteristic	580 V / 5 sec. – withstand
Temporary overvoltage (TOV) ( $U_T$ ) – Characteristic	765 V / 120 min. – safe failure
Operating temperature range ( $T_U$ )	-40 °C ... +80 °C
Operating state / fault indication	green / red
Number of ports	1
Cross-sectional area (min.)	1.5 mm <sup>2</sup> solid / flexible
Cross-sectional area (max.)	35 mm <sup>2</sup> stranded / 25 mm <sup>2</sup> flexible
For mounting on	35 mm DIN rails acc. to EN 60715
Enclosure material	thermoplastic, red, UL 94 V-0
Place of installation	indoor installation
Degree of protection	IP 20
Capacity	3 module(s), DIN 43880
Approvals	KEMA, UL, VdS
Type of remote signalling contact	changeover contact
a.c. switching capacity	250 V / 0.5 A
d.c. switching capacity	250 V / 0.1 A; 125 V / 0.2 A; 75 V / 0.5 A
Cross-sectional area for remote signalling terminals	max. 1.5 mm <sup>2</sup> solid / flexible
Weight	362 g
Customs tariff number	85363030
GTIN	4013364120716
PU	1 pc(s)

We reserve the right to introduce changes in performance, configuration and technology, dimensions, weights and materials in the course of technical progress. The figures are shown without obligation.