


MGS30

MG S 30 24 05 -□

① ② ③ ④ ⑤ ⑥



- ① Series name
- ② Single output
- ③ Output wattage
- ④ Input voltage
- ⑤ Output voltage
- ⑥ Optional
- G : Capacitor between Input and Output is removed.
- R : with Remote ON/OFF (Positive logic control)

MODEL	MGS30123R3	MGS301205	MGS301212	MGS301215	MGS30243R3	MGS302405	MGS302412	MGS302415
MAX OUTPUT WATTAGE[W]	26.4	30	30	30	26.4	30	30	30
DC OUTPUT	VOLTAGE[V] *1	3.3	5	12	15	3.3	5	12
	CURRENT[A]	8	6	2.5	2	8	6	2.5

SPECIFICATIONS

	MODEL	MGS30123R3	MGS301205	MGS301212	MGS301215	MGS30243R3	MGS302405	MGS302412	MGS302415
INPUT	VOLTAGE[V]	DC9 - 18				DC18 - 36			
	CURRENT[A] *2	2.45typ	2.75typ	2.78typ	2.78typ	1.21typ	1.36typ	1.36typ	1.36typ
	EFFICIENCY[%] *2	90typ	91typ	90typ	90typ	91typ	92typ	92typ	92typ
OUTPUT	VOLTAGE[V]	3.3	5	12	15	3.3	5	12	15
	CURRENT[A]	8	6	2.5	2	8	6	2.5	2
	LINE REGULATION[mV]	13.2max	20max	48max	60max	13.2max	20max	48max	60max
	LOAD REGULATION[mV]	13.2max	20max	48max	60max	13.2max	20max	48max	60max
	RIPPLE[mVp-p] *3	-20 to +60℃	75max	75max	100max	100max	75max	75max	100max
		-40 to -20℃	100max	100max	120max	120max	100max	100max	120max
	RIPPLE NOISE[mVp-p] *3	-20 to +60℃	75max	75max	100max	100max	75max	75max	100max
		-40 to -20℃	150max	150max	150max	150max	150max	150max	150max
	TEMPERATURE REGULATION[mV]	-20 to +60℃	50max	50max	150max	180max	50max	50max	150max
		-40 to +60℃	80max	80max	240max	290max	80max	80max	240max
PROTECTION CIRCUIT AND OTHERS	DRIFT[mV] *4	20max	20max	48max	60max	20max	20max	48max	60max
	START-UP TIME[ms]	30max (Minimum input, Io=100%)							
	OUTPUT VOLTAGE ADJUSTMENT RANGE	Fixed (TRM pin open) ±10% adjustable by external VR							
	OUTPUT VOLTAGE SETTING[V] *5	3.296 - 3.404	4.975 - 5.137	11.857 - 12.243	14.839 - 15.321	3.296 - 3.404	4.975 - 5.137	11.857 - 12.243	14.839 - 15.321
	OVERCURRENT PROTECTION	Works over 105% of rating and recovers automatically							
PROTECTION CIRCUIT AND OTHERS	OVERVOLTAGE PROTECTION[V]	Works over 120 to 160% of rating							
	REMOTE ON/OFF	Provided (Negative logic L:ON, H:OFF)							

MODEL	MGS30483R3	MGS304805	MGS304812	MGS304815
MAX OUTPUT WATTAGE[W]	26.4	30	30	30
DC OUTPUT	VOLTAGE[V] *1	3.3	5	12
	CURRENT[A]	8	6	2.5

SPECIFICATIONS



	MODEL	MGS30483R3	MGS304805	MGS304812	MGS304815
INPUT	VOLTAGE[V]	DC36 - 76			
	CURRENT[A] *2	0.61typ	0.68typ	0.68typ	0.68typ
	EFFICIENCY[%] *2	91typ	92typ	92typ	92typ
OUTPUT	VOLTAGE[V]	3.3	5	12	15
	CURRENT[A]	8	6	2.5	2
	LINE REGULATION[mV]	13.2max	20max	48max	60max
	LOAD REGULATION[mV]	13.2max	20max	48max	60max
	RIPPLE[mVp-p] *3	-20 to +60℃	75max	75max	100max
		-40 to -20℃	100max	100max	120max
	RIPPLE NOISE[mVp-p] *3	-20 to +60℃	75max	75max	100max
		-40 to -20℃	150max	150max	150max
	TEMPERATURE REGULATION[mV]	-20 to +60℃	50max	50max	150max
		-40 to +60℃	80max	80max	240max
PROTECTION CIRCUIT AND OTHERS	DRIFT[mV] *4	20max	20max	48max	60max
	START-UP TIME[ms]	30max (Minimum input, Io=100%)			
	OUTPUT VOLTAGE ADJUSTMENT RANGE	Fixed (TRM pin open) ±10% adjustable by external VR			
	OUTPUT VOLTAGE SETTING[V] *5	3.296 - 3.404	4.975 - 5.137	11.857 - 12.243	14.839 - 15.321
	OVERCURRENT PROTECTION	Works over 105% of rating and recovers automatically			
PROTECTION CIRCUIT AND OTHERS	OVERVOLTAGE PROTECTION[V]	Works over 120 to 160% of rating			
	REMOTE ON/OFF	Provided (Negative logic L:ON, H:OFF)			

GENERAL SPECIFICATIONS

ISOLATION	INPUT-OUTPUT	DC1,500V 1minute, Cutoff current = 10mA, DC500V 1,000M Ω min (20 $\pm$ 15 $^{\circ}$ C)
	INPUT-CASE	DC1,000V 1minute, Cutoff current = 10mA, DC500V 1,000M Ω min (20 $\pm$ 15 $^{\circ}$ C)
	OUTPUT-CASE	DC1,000V 1minute, Cutoff current = 10mA, DC500V 1,000M Ω min (20 $\pm$ 15 $^{\circ}$ C)
ENVIRONMENT	OPERATING TEMP., HUMID. AND ALTITUDE	-40 to +85 $^{\circ}$ C, 20 to 95%RH (Non condensing) (Required Derating), 3,000m (10,000feet) max
	STORAGE TEMP., HUMID. AND ALTITUDE	-40 to +100 $^{\circ}$ C, 20 to 95%RH (Non condensing), 9,000m (30,000feet) max
	VIBRATION	10 - 55Hz, 98.0m/s 2 (10G), 3minutes period, 60minutes each along X, Y and Z axis
SAFETY	IMPACT	490.3m/s 2 (50G), 11ms, once each along X, Y and Z axis
	AGENCY APPROVALS	UL60950-1, C-UL, EN60950-1
OTHERS	CASE SIZE/WEIGHT	25.4 X 9.9 X 50.8mm [1 X 0.39 X 2 inches] (W X H X D) / 40g max
	COOLING METHOD	Convection/Forced air

- *1 MGW30xx05/MGW30xx12/MGW30xx15 is available as single output, +10V/+24V/+30V
- *2 Rated input 12V, 24V or 48V DC $I_o=100\%$
- *3 Ripple and Ripple Noise is measured by using test board with ceramic capacitor 22 μ F at 50mm from output pins. (20MHz Oscilloscope)
- *4 Drift is the DC output accuracy for eight hours period after a half-hour warm-up at 25 $^{\circ}$ C.
- *5 Rated input voltage (DC12V, DC24V, DC48V), rated output wattage, ambient temperature at 25 $^{\circ}$ C.
- * Parallel operation with other model is not possible.

External view



- ※ Tolerance ± 0.5 [± 0.02]
- ※ Dimensions in mm, []=inches
- ※ Pin terminal material : Copper
- ※ Plating treatment of terminal : Lead free plating
- ※ Case material : Brass
- ※ Plating treatment of case : Nickel plating
- ※ Bottom Cover : FR4 ($t=0.6$) [$t=0.024$]
- ※ Please keep enough creepage distance with the pattern on PCB and other components.
- ※ Weight 40g max