

## Hi Spot 63 Superia Extralife

HS63 SU 240V 50W 25° E27 SV1

0021128



### Range features

- Halogen light without the need for a transformer
- Unique, patented, spiral faceted aluminised reflector
- 100% dimmable
- For use in mains voltage E27 cap downlights, spotlights and luminaires
- For accent or decorative lighting in retail, commercial and domestic applications
- Suitable for outdoor use when protected from direct contact with water
- Average rated life 2500hrs - 25% longer life than conventional PAR halogen lamps



### PRODUCT OVERVIEW

Ordering number	0021128
Light colour	829 Warm white
Technology	Halogen
Energy class	D
Average life (Rated) (h)	3000
Lamp finish	Aluminium
Lamp shape	Reflector
Dimmable	Yes
Cap/Base	E27
Type	PAR 20
EAN code	5410288211282
CRI (Ra)	100
Beam angle(°)	25
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	360
Watt (Nominal) (W)	50
Equivalent watt (W)	58
Voltage (V)	240

## Hi Spot 63 Superia Extralife

HS63 SU 240V 50W 25° E27 SV1

0021128

### DATA TABLE

#### General data

<b>Ordering number</b>	0021128
<b>Technology</b>	Halogen
<b>Average life (Rated) (h)</b>	3000
<b>Average life (Nominal) (h)</b>	3000
<b>Energy class</b>	D
<b>Energy saving lamp</b>	No
<b>Lamp shape</b>	Reflector
<b>Lamp finish</b>	Aluminium
<b>Dimmable</b>	Yes
<b>Cap/Base</b>	E27
<b>Type</b>	PAR 20
<b>EAN code</b>	5410288211282
<b>E-number FI</b>	4749293
<b>E-number SE</b>	8355902
<b>Long description</b>	Halogen light without the need for a transformer. Unique, patented, spiral faceted aluminised reflector. 100% dimmable. For use in mains voltage E27 cap downlights, spotlights and luminaires. For accent or decorative lighting in retail, commercial and domestic applications. Suitable for outdoor use when protected from direct contact with water. Average rated life 2500hrs - 25% longer life than conventional PAR halogen lamps
<b>Product name</b>	HS63 SU 240V 50W 25° E27 SV1
<b>Lamp mercury content (mg)</b>	0
<b>Starting time (max) (s)</b>	0
<b>Warm-up time to 60% of full light (max) (s)</b>	Instant Full Light
<b>Control gear required</b>	No
<b>Fixture rating</b>	Open
<b>IEC Reference</b>	IEC 60357
<b>IEC Reference 2</b>	IEC 60432-3
<b>IEC Reference 3</b>	IEC 60630
<b>Intended purpose</b>	General lighting
<b>No. of switching cycles before premature failure (min)</b>	>12000
<b>Special purpose lamp</b>	No
<b>Transformer required</b>	No
<b>Sales pack quantity</b>	15

# Hi Spot 63 Superia Extralife

HS63 SU 240V 50W 25° E27 SV1

**0021128**

## Optical data

Light colour	829 Warm white
CRI (Ra)	100
Beam angle (Rated) (°)	25
Suitable for accent lighting	Yes
Beam angle(°)	25
Colour temperature (K)	2900
Useful luminous flux (Rated) (lm)	360
Lumen maintenance at end of nominal life (%)	80
Luminous flux (Nominal) (lm)	360
Peak intensity (cd)	1000

## Electrical data

kWh per 1000 hours burning time	50
Equivalent watt (W)	58
Watt (Rated) (W)	50
Watt (Nominal) (W)	50
Voltage (V)	240
Current (A)	0.21
Lamp power factor	1

## Physical data

Weight (kg)	0.11
Lamp Length (mm) - C/L	88
Max. Lamp Diameter (mm) - D	63
Lamp dimension equal to filament lamp equivalent	Yes
Designed for optimum use in non standard conditions	No
Single packaging type	Box/Sleeve
Single package dimensions (L x W x H) (cm)	8.70 x 7.80 x 7.80
Outer package dimensions (L x W x H) (cm)	42.50 x 25.50 x 10.50


## Hi Spot 63 Superia Extralife

HS63 SU 240V 50W 25° E27 SV1


0021128

### PHOTOMETRY

#### Hi-Spot 63 / 50W



### TECHNICAL DRAWINGS



### ENERGY LABEL

