

Datasheet

RS Pro NPI43C Series Wire-wound SMD Inductor 330 μ H \pm 20% Wire-Wound 140mA Idc

RS Stock No: 740-9454



Product Details

RS Pro wire-wound SMD inductor offers inductance of 330 μ H and withstands DC current up to 140 mA. It works with DC-DC converters and DC-AC inverters. This compact filter is suitable for both flow and reflow soldering.

Features and Benefits

- High current, small size (up to 4 amps)
- Surface mountable construction
- High inductance (up to 680 μ h)
- Suitable for use in DC/DC converters, DC/AC inverters
- Lead free compatible

Specifications:

Inductor Construction	Wire Wound
Shielded	No
Depth	4 mm
Dimensions	4.5 x 4 x 3.2 mm
Height	3.2 mm
Length	4.5 mm
Maximum DC Current	140 mA
Maximum DC Resistance	4 Ω
Maximum Operating Temperature	+85°C
Minimum Operating Temperature	-40°C
Tolerance	$\pm 20\%$
Inductance	330 μH
Package/Case	43
Package Type	Tape & Reel