


Cam followers



Dimensions				Basic load ratings		Fatigue load limit	Maximum radial loads		Limiting speed	Mass	Designation
D	d	B	C	dynamic C	static C ₀	P _u	dynamic F _r	static F _{0r}	r/min	kg	-
mm				kN		kN	kN				
16	6	28	11	3,14	3,2	0,345	2,9	4,15	6000	0,018	KR 16 PPA



Appertaining grease nipple(s) NIP A1
Appertaining hexagonal nut
 Size, mm M 6
 Rec. tightening torque, Nm 3