


FEMALE END VIEW




1 = GRN
2 = RED/BLK
3 = RED/WHI



SPECIFICATIONS

CONTACT CARRIER MATERIAL	NYLON
MOLDED HEAD MATERIAL/COLOR	THERMOPLASTIC PUR/YELLOW
CONTACT MATERIAL/PLATING	GOLD-PLATED BRASS
COUPLING NUT	NICKEL-PLATED BRASS
RATED CURRENT [A]	4.0 A
RATED VOLTAGE [V]	250 V
OUTER JACKET MATERIAL/COLOR	PVC/YELLOW
CONDUCTOR INSULATION MATERIAL	PVC
NUMBER OF CONDUCTORS [AWG]	3x22 AWG
TEMPERATURE RANGE	-40°C to +105°C (-40°F to +221°F)
PROTECTION CLASS	MEETS NEMA 1,3,4,6P AND IEC IP67



* METERS
SEE NOTE 1

CABLE LENGTH	TOLERANCE
ALL LENGTHS	+ 4% (OR 50mm) OF LENGTH - 0% (OR 0mm) OF LENGTH WHICHEVER IS GREATER
STRIP LENGTH	TOLERANCE
0-7mm	±0.5mm
8-29mm	±1.0mm
30-49mm	±2.0mm
50-69mm	±3.0mm
70-100mm	±4.0mm
OVER 100mm	±5.0mm

NOTES:

1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.
2. STRIP AND TIN LENGTHS ARE FOR REFERENCE ONLY; SOME LENGTHS MAY NOT BE STRIPPED AND TINNED.

SOURCE DRAWING - FOR REFERENCE ONLY

OVER 100mm		±5.0mm	
------------	--	--------	--

NOTES:			
1. "*" INDICATES CABLE LENGTH IN METERS. CONTACT TURCK TO ORDER SPECIFIC LENGTHS.			
2. STRIP AND TIN LENGTHS ARE FOR REFERENCE ONLY; SOME LENGTHS MAY NOT BE STRIPPED AND TINNED.			
A DRAWING RELEASE		RDS	01/28/02
REV	DESCRIPTION	BY	DATE
			ECO NO.

RELATED DOCUMENTS		3RD ANGLE PROJECTION		THIS DOCUMENT IS PROPERTY OF TURCK INC. USE OF THIS DOCUMENT WITHOUT WRITTEN PERMISSION IS PROHIBITED.		TURCK inc <i>High Technology Sensors and Automation Controls</i>		3000 CAMPUS DRIVE MINNEAPOLIS, MN 55441 1-800-544-7769 (763) 553-7300 (763) 553-0708 fax turck.com					
1.			DRAFT	JBU	DATE 02/16/01	SCALE 1=1.0	DESCRIPTION	KB 3T-*					
2.													
3.													
4.													
MATERIAL		TOLERANCES UNLESS OTHERWISE SPECIFIED		UNIT OF MEASUREMENT		IDENTIFICATION NO.		REV					
SEE SPECIFICATIONS		.X ±0.02 .XX ±0.01 .XXX ±0.005		INCH [MILLIMETER]				A					
FINISH		ALL MILLIMETER DIMENSIONS ARE REFERENCE ONLY		DO NOT SCALE THIS DRAWING		FILE: MICRO-C\777000598		SHEET 1 OF 1					
SEE SPECIFICATIONS													