

Datasheet

## RS Pro 315mA Radial Non-Resettable Wire Ended Fuse, 250 V

RS Stock No: **767-5020**



### Product Details

RS Pro radial non-resettable fuse withstands currents up to 315 mA and voltages up to 250 V. It has thermoplastic body for added durability. This slow blow fuse forms a convenient and reliable solution to a vast array of application requirements.

### Features and Benefits

- Slow blow fuse
- Base and cap in black thermoplastic
- Round pins in tin plated copper
- Vibration MIL-STD-202G
- Salt spray MIL-STD-202G
- Insulation resistance MIL-STD-202G
- Resistance to solder heat MIL-STD-202G
- Thermal shock MIL-STD-202G

**Specifications:**

|   |  |
|---|--|
| Body Height                                   | 7.7 mm                                   |
| Body Length                                   | 8.35 mm                                  |
| Body Material                                 | Thermoplastic                            |
| Body Width                                    | 4.3 mm                                   |
| Breaking Capacity (at Maximum Voltage Rating) | 35 A at 250 V ac                         |
| Current Rating                                | 315 mA                                   |
| Lead Orientation                              | Radial                                   |
| Maximum Operating Temperature                 | +125°C                                   |
| Minimum Operating Temperature                 | -55°C                                    |
| Voltage Rating                                | 250 V                                    |
| Voltage Rating                                | 250 V                                    |
| Wire Diameter                                 | 0.62 mm                                  |
| Wire Length                                   | 22 mm, 4.3 mm                            |
| Wire Pitch                                    | 5.08 mm                                  |
| Fuse Type                                     | Time Lag                                 |
| Nominal Resistance                            | 0.38 Ω                                   |
| Standards Met                                 | SEMKO, VDE, TUV, CSA, UL, CCC, KTL, RoHS |