



Ordering number CA12062_EMILY-D

Family	Emily	FWHM	(simulated) 14
Type	Assembly	Efficiency	88 %
LED	XM-L HVW	cd/lm	9.400
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	14.9 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		


Ordering number CA12064_EMILY-M

Family	Emily	FWHM	(simulated) 19
Type	Assembly	Efficiency	90 %
LED	XM-L HVW	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		


Ordering number CA12066_EMILY-O

Family	Emily	FWHM	(simulated) 12+48
Type	Assembly	Efficiency	86 %
LED	XM-L HVW	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		


Ordering number CA12068_EMILY-O-90

Family	Emily	FWHM	(simulated) 48+12
Type	Assembly	Efficiency	86 %
LED	XM-L HVW	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

**Ordering number CA12070_EMILY-M2**

Family	Emily	FWHM	(simulated) 30
Type	Assembly	Efficiency	88 %
LED	XM-L HVW	cd/lm	-
Color	Clear	Gerber File	Available
Diameter	26 mm		
Height	15 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	Pin, tape		
Status	Ready		

NOTE: The typical divergence will be changed by different color, chip size and chip position tolerance. The typical total divergence is the full angle measured where the luminous intensity is half of the peak value.



PRODUCT DATASHEET

Emily series

last update 14/11/2012

GENERAL INFORMATION


- Product series especially designed & optimized for XM-L HVW series of LEDs.
- Special care taken to make light distribution as uniform as possible.
- Lens material optical grade PMMA with high UV and temperature resistance. Allows use of high current and temperature conditions.

Please find more information about used material from below:


http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20UL94_Yellow%20Card.pdf

<http://ledil.fi/sites/default/files/Documents/Technical/Material/PMMA%20N%20PLEXIGLAS-Datasheet.pdf>

Luminaire: Ledil Oy CA12062_EMILY-D (Cree XM-L HVW 285lm 50mA) Efficiency=88%
Lamps: 1 x Cree XM-L HVW 285lm 50mA



Luminaire: Ledil Oy CA12062_EMILY-D (Cree XM-L HVW 285lm 50mA) Efficiency=88%
Lamps: 1 x Cree XM-L HVW 285lm 50mA



cd/klm

— C0 - C180

— C90 - C270