



Main

Device application	Distribution
Range of product	Librio
Product or component type	Miniature circuit-breaker
Device short name	C40N
Poles description	3P + N
Number of protected poles	3
Neutral position	Left
[In] rated current	6 A
Network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	Icu conforming to IEC 60947-2 - 400 V AC 50 Hz Icn conforming to EN 60898 - 400 V AC 50 Hz
Suitability for isolation	Yes conforming to IEC 60947-2
Standards	EN 50027 EN 60898 EN 61009 IEC 60947-2

Complementary

Network frequency	50 Hz
[Ue] rated operational voltage	400 V AC 50 Hz between phase and neutral
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	6000 A conforming to EN 60898 AC 50 Hz
Limitation class	3 conforming to EN 60898
[Ui] rated insulation voltage	400 V AC 50 Hz conforming to EN 60898
[Uimp] rated impulse withstand voltage	4 kV
Control type	Toggle
Local signalling	ON/OFF indication
Mounting mode	Fixed
Mounting support	35 mm symmetrical DIN rail
Comb busbar distribution block compatibility	Librio
9 mm pitches	6
Mechanical durability	20000 cycles
Electrical durability	20000 cycles
Connections - terminals	Tunnel type terminals rigid wire(s) 1...16 mm ² max Tunnel type terminals flexible wire(s) 1.5...16 mm ² max
Earth-leakage protection	Separate block

Environment

IP degree of protection	IP4
pollution degree	3 conforming to IEC 60947-2
tropicalisation	2
relative humidity	95 % 55 °C
operating altitude	2000 m
ambient air temperature for operation	-5...70 °C
ambient air temperature for storage	-40...100 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Contractual warranty

Warranty period

18 months