


86092645113765E1LF - DIN 41612 : Right
Angle Header Solder-to-Board Style B 64
ways, Class I



www.fci.com

Mating Half

 86092646114765V1LF

Specifications

Mechanical	
Durability (Mating cycles)	500
Insertion force	<= 0.94N per Contact
Withdrawal Force	>= 0.15N per Contact
Dimensional	
Length (Tail)	2.75 mm (.108 in.)
Electrical	
Current rating	1.5A at 20°C
Resistance (Contact)	<= 20 milli ohms
Resistance (Insulation)	≥ 1000000 M-ohms
Voltage rating	1000V rms
General	
Gender	Header
Housing Style	Style B
Loading Pattern	All
Number of contacts (Total)	64
Number of rows (Loaded)	A+B
Orientation	Right Angle
Post type	Solder-to-Board
Product Style	Board Connector
Fixing Clip	No
Mounting	
Board / Rack attachment	Board
Mounting ears	Yes
Other Features	
Most Popular Configuration	Yes
Packaging (Type)	Tray
Type	Signal
Physical	
Color (Housing)	Grey
Material (Contact)	

	Copper Alloy
Material (Housing)	Glass - Filled Thermoplastic Polyester
Plating (Contact area)	Selective Gold over Nickel
Plating (Tail)	Matte Tin
Plating Specification (Contact area)	Class I
Temperature (Range)	-55°C to +125°C