

Drills

Shop line

Last update : 15/01/07




Guaranteed
2 years

> BENCH DRILLS 13 A / 22 A / 22 FE

Characteristics :

- Spindle mounted on ball bearings
- Semi steel column
- Notched belt transmission
- Capstan arm with ergonomic rubber handles
- Safety microswitch on pulley housing
- On/off switch with undervoltage coil
- Swing-away and adjustable protection guard
- Mushroom head emergency stop
- Table inclinable up to 45°
- Table with lubricant recovery system (22 FE)
- Rack and pinion table movement (22 A and 22 FE)
- Standard self-tightening B18 chuck, chuck arbour, punch key, screw vise and set of flanges

	Max drilling capacity (mm)	Morse taper	Ø column (mm)	Spindle travel (mm)	Number of speed	Spindle travel (rpm)	Dimensions a x b x c (mm)	d (mm)	e (mm)	f (mm)	Table size Ø (mm)	Motor power (kw)			
13 A	13	JT2	60	70	5	500 - 2500	540 x 720 x 340	125	412	250	230	0,33			20501008
22 A	22	CM2	72	90	12	280 - 2220	650 x 1005 x 380	170	640	455	290	0,45			20501014
22 FE	22	CM2	80	90	12	240 - 2500	680 x 998 x 380	185	585	360	315	0,75	 		20501009 20501015



a : depth
b : height
c : width
d : spindle / column distance
e : Spindle / base distance
f : Spindle / table distance



13 A



22 A

22 FE



Capstan arm with ergonomic rubber handles

Accessories :

• Vises :

	For drill	Type	set of flanges	Width of jaws (mm)	Height of jaws (mm)	Groove separation (mm)	Max opening (mm)		
€ 75	13 A	screw model	not included	75	20	120	80	2,2	20598001
€ 100	22 A	screw model	not included	100	25	135	110	2,8	20598002
€ 125	22 FE / 22 FC	screw model	not included	125	28	155	115	4,8	20598037
€ 150	30 FC / 40 FC	screw model	not included	150	35	185	140	7,5	20598003
S 100	22 A / 22 FE / 22 FC	rapid closing	not included	105	30	125	110	7	20598004
S 150	40 FC	rapid closing	not included	155	40	195	155	11,5	20598005



E 75



E 100



E 125



E 150



S 100



S 150

• Complete vise fixation system* :

Set of flanges	
	20598041

- * 2 studs M12 x 80
- 2 flat washers Ø 12
- 2 bars M12 x 14
- 2 nuts M12 x 18



• Self-tightening chucks :

	1 to 13 mm - JT2 	1 to 16 mm - B18
13 A	20598007	-
22 A / 22 FE / 22 FC / 30 FC / 40 FC	-	20598036

