

# Datasheet

## DIN Rail control Panel isolation Transformers IP21

# RS Pro

The standard 1 phase EI panel transformers with IP21 degree of protection, DIN rail TS35 mount and screw mount sign according to the following specifications.

- High quality control, isolating and safety transformers designed for use in general applications
- Various options for primary winding
- Enclosed in box IP21
- Detailed product specification on permanent label
- High efficiency, low regulation design
- 100% electrical and flash tested



### Specifications

Power: 40–400 VA  
 Frequency: 50/60 Hz  
 Primary: See ordering details  
 Secondary: See ordering details  
 Construction: Class I  
 Isolation: 4kV or 4.6 kV RMS  
 Temp. Class: B (130°)  
 According to: EN61558-1  
 EN61558-2-2  
 EN61558-2-4  
 EN61558-2-6



### Ordering details:

RS Stock number	Power VA	Specification	Input voltage	Output voltage	No-load voltage
8802609	40	40VA 24Vac Transformer	-15-0-15-230-400	24	26.1
8802558	40	DIN Rail Transformer 40VA 24-48V	-15-0-15-230-400	2 X 24	2 X 26.3
8802570	40	DIN Rail Transformer 40VA 115-230V	-15-0-15-230-400	2 X 115	2 x 124.8
8802501	40	Control Panel Transformer 40VA 2x12V	0-230-400	2 X 12	2 x 13.2
8802523	40	Control Panel Transformer 40VA 2x0-24V	0-230-400	2 X 24	2 x 26.3
8802514	40	Control Panel Transformer 40VA 2x115V	0-230-400	2 X 115	2 x 125.4
8802618	63	63VA 24Vac Transformer	-15-0-15-230	24	26.4
8802615	63	63VA 24Vac Single Phase Transformer	-15-0-15-230-400	24	26.4




**Ordering details (Continued):**

RS Stock number	Power VA	Specification	Input voltage	Output voltage	No-load voltage
8802567	63	DIN Rail Transformer 63VA 24-48V	-15-0-15-230-400	2 x 24	2 x 26.3
8802589	63	DIN Rail Transformer 63va 115-230V	-15-0-15-230-400	2 x 115	2 x 125.5
8802491	63	Control Panel Transformer 63VA 2x12V	0-230-400	2 x12	2 x 13.2
8802539	63	Control Panel Transformer 63VA 2X24V	0-230-400	2 x 24	2 x 26.4
8802551	63	Control Panel Transformer 63VA 115V CT	0-230-400	2 x 57.5	2 x 62.7
8802602	100	100VA 24Vac Transformer	-15-0-15-230	24	25.8
8802611	100	Control Panel Transformer 100VA 24V	-15-0-15-230-400	24	25.8
8802560	100	DIN Rail Transformer 100VA 24-48V	-15-0-15-230-400	2 x 24	2 x 25.8
8802582	100	DIN Rail Transformer 100VA 115-230V	-15-0-15-230-400	2 x 115	2 x 122.5
8802548	100	Control Panel Transformer 100VA 2X0-12V	0-230-400	2 x 12	2 x 12.9
8802510	100	Control Panel Transformer 100VA 2X24V	0-230-400	2 x 24	2 x 25.8
8802542	100	Control Panel Transformer 100VA 115V CT	0-230-400	2 x 57.5	2 x 61.3
8802508	100	Control Panel Transformer 100VA 2X115V	0-230-400	2 x 115	2 x 122.5
8802564	160	DIN Rail Transformer 160VA 24-48V	-15-0-15-230-400	2 x 24	2 x 25.8
8802586	160	DIN Rail Transformer 160VA 115-230V	-15-0-15-230-400	2 x 115	2 x 121.9
8802598	160	Transformer Panel Mount 24-48Vac 160VA	0-230-400	2 x 24	2 x 25.8
8802520	160	Control Panel Transformer 160VA 115V	0-230-400	2 x 57.5	2 x 61.4
8802592	160	Transformer Panel Mount 115-230Vac	0-230-400	2 x115	2 x 121.9
8802536	220	Control Panel Transformer 220VA 2x0-12V	0-230-400	2 x 12	2 x 12.7
8802554	220	Control Panel Transformer 220VA 2X24V	0-230-400	2 x 24	2 x 25.4
8802545	220	Control Panel Transformer 220VA 115V CT	0-230-400	2 x 57.5	2 x 60.8
8802517	220	Control Panel Transformer 220VA 2X115V	0-230-400	2 x115	2 x 121.6
8802573	250	DIN Rail Transformer 250VA 24-48V	-15-0-15-230-400	2 x 24	2 x 25.4
8802595	250	DIN Rail Transformer 250VA 115-230V	-15-0-15-230-400	2 x 115	2 x 121.9
8802532	310	Control Panel Transformer 310VA 2X0-12V	0-230-400	2 x 12	2 x 12.9
8802526	310	Control Panel Transformer 310VA 2X24V	0-230-400	2 x 24	2 x 25.8
8802504	310	Control Panel Transformer 310VA 230V	0-230-400	2 x 115	2 x 123.7
8802505	400	400VA 24Vac Transformer	-15-0-15-230	24	25.2
8802576	400	DIN Rail Transformer 400VA 24-48V	-15-0-15-230-400	2 X 24	2 x 25.2

Subject to errors and changes in data sheets.

**Dimensions:**



Power	Overall Size	Fixing	Hole size	Weight
[VA]	A x B x H [mm]	E x F [mm]	[mm]	[kg]
40	90 x 106 x 87	68.5 x 90	4 x R4.5	1.4
63	90 x 106 x 87	68.5 x 90	4 x R4.5	1.5
100	90 x 106 x 107	68.5 x 90	4 x R4.5	2.3
160	102 x 116 x 116	82 x 102	4 x R5.0	4.8
220	102 x 116 x 110	82x 102	4 x R5.0	4.9
250	96 x 116 x 127	82 x 102	4 x R5.0	5.0
310	102 x 116 x 127	96 x 121	4 x R5.5	4.2
400	126 x 136 x 117	96 x 121	4 x R5.5	5.0