







THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY



TYPE "B"




△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min


CUSTOMER DRAWING

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-292173	—

REV	C2
-----	----



THREE KINDS OF DIFFERENT POCKETS AS 1 SET
USED FOR 7P ONLY



TYPE "A"





Fig-2

△ PEELING RESISTANCE : 0.196N-0.686N (20gf-70gf)
SPEED : 300mm/min

CUSTOMER DRAWING

A3 00779 C-292173

REV	C2
-----	----

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

DIST

REVISIONS

ES

00

P

LTR

DESCRIPTION




DATE

DWN

APVD

SEE SHEET 1

(AS SHOWN : -4)



NOTES:

1. MATERIAL: HSG-6T PA(G.F.30%)(UL94V-0)

COLOR: BLACK, NATURAL

POST: TIN BRASS

TAIL: TIN BRASS




2. OCCUPANT AREA ON PC BOARD

4P&ABOVE POS.

2P&3P

3. TO BE MEASURED WITH CONNECTOR PLACED ON HORIZONTAL DATUM SURFACE, FLOAT OF SOLDER TINE AND TAIL FROM DATUM SURFACE IS 0.1mm MAX

16.0	15.6	19.8	22.0	9	1-292173-9	292173-9
14.0	13.6	17.8	20.0	8	1- -8	-8
12.0	11.6	15.8	18.0	7	1- -7	-7
10.0	9.6	13.8	16.0	6	1- -6	-6
8.0	7.6	11.8	14.0	5	1- -5	-5
6.0	5.6	9.8	—	4	1- -4	-4
4.0	—	7.8	—	3	1- -3	-3
2.0	—	5.8	—	2	1-292173-2	292173-2
A	B	C	D	Pos.	NATURAL	BLACK
						P/N

NO ACCUMULATED TOLERANCE
RECOMMENDED P.C.BOARD LAYOUT
(P.C.B. THK:0.8mm MIN)

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

10>* : ±0.2
30>*10 : ±0.25
100>*30 : ±0.3
ANGEL : ±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC ±—
1 PLC ±—
2 PLC ±—
3 PLC ±—
4 PLC ±—
ANGLES ±—
FINISH

MATERIAL

SEE NOTE

SEE NOTE

DWN

CHK

APVD

PRODUCT SPEC

108-60016

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

SMT TYPE POST HDR ASS'Y (H)

WITH BOSS & TAIL TYPE

(TE CT CONN. 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C-292173

SCALE 5:1

SHEET 3 OF 6

REV C2

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

-,-

© COPYRIGHT - By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD


- SEE SHEET 1

-


-

-


LAYOUT FOR 292173-X,1-292173-X



5 POS. & ABOVE POS.




3 POS.



2 POS.

RECOMMENDED P.C. BOARD LAYOUT
(P.C.B THK:0.8mm MIN)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
MMTOLERANCES UNLESS
OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	± -

MATERIAL

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

STE

TE Connectivity

NAME

SMT TYPE POST HDR ASS'Y (H)
WITH BOSS & TAIL TYPE
(TE CT CONN. 2mm PITCH)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779


C-292173

SCALE 5:1

SHEET 4 OF 6

REV C2

LAYOUT FOR 2-292173-X,3-2-292173-X



2POS

RECOMENOE P.C.BOARD LAYOUT
(P.C.B THK:0.8mm MIN)

CUSTOMER DRAWING

	MATERIAL
--	----------

ANGLES	
FINISH	

CU

SMT TYPE POST HDR ASS'Y (H)
W/O,WITH TAIL TYPE
(TE CT CONN. 2mm PITCH)

C-292173

REV	
-----	--

SCALE 5:1

SHEET 6 OF 6

REV C2