

# Zack marker strip - ZB10,LGS:FORTL.ZAHLEN - 1053014

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Zack marker strip, Strip, white, labeled, Can be labeled with: Plotter, Printed horizontally: Consecutive numbers 1 - 10, 11 - 20, etc. up to 991 - 1000, Mounting type: Snap into tall marker groove, For terminal block width: 10.2 mm, Lettering field: 10.15 x 10.5 mm

The illustration shows versions  
ZB 10 - UNPRINTED, -  
LGS:CONSEC.NOS, -  
QR:CONSEC.NOS and -SO/CMS

## Product Features

- ✓ Labeling service: Phoenix Contact can custom-label all zack marker strip markers according to your requirements
- ✓ The ZB zack marker strip system is a marking solution for modular terminal blocks and electronics modules with tall marker grooves

## Key commercial data

|                                      |                                                                                                         |
|--------------------------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit                         | 1 pc                                                                                                    |
| Minimum order quantity               | 10 pc                                                                                                   |
| GTIN                                 | <br>4 017918 016685 |
| Weight per Piece (excluding packing) | 2.32 GRM                                                                                                |
| Custom tariff number                 | 39269097                                                                                                |
| Country of origin                    | Germany                                                                                                 |

## Technical data

### Dimensions

|           |       |
|-----------|-------|
| Width (a) | 10 mm |
|-----------|-------|

### Ambient conditions

|                                 |                   |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 100 °C |
|---------------------------------|-------------------|

### General

|                                         |                                                             |
|-----------------------------------------|-------------------------------------------------------------|
| Note                                    | 10 identically marked strips make up one packing unit (PU). |
| Color                                   | white                                                       |
| Components                              | free from silicone and halogen                              |
| Inflammability class according to UL 94 | V2                                                          |

# Zack marker strip - ZB10,LGS:FORTL.ZAHLEN - 1053014

## Technical data

### General

|                                     |                                                            |
|-------------------------------------|------------------------------------------------------------|
| Material                            | PA                                                         |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1)                                |
|                                     | VDE 0411-1                                                 |
| Printing direction                  | Printed horizontally                                       |
| Printing                            | Consecutive numbers 1 - 10, 11 - 20, etc. up to 991 - 1000 |
| Number of individual labels         | 10                                                         |
| Number of individual labels per row | 10                                                         |
| Number of marker strips             | 10                                                         |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27141137 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |