




10 9 8 7 6 5 4 3 2 1



注記
NOTES

1. 各部の反りは0.5最大。
WARPING : 0.5 MAX.
2. サークットNO.はNO."I"のみ表示。
CIRCUIT NO. : I ONLY.
3. ELV及びRoHS適合品。
ELV AND RoHS COMPLIANT.



52.62	47.52	09-50-1123	5196-12	12
48.66	43.56	↑ -1113	↑ -11	11
44.7	39.6	-1103	-10	10
40.74	35.64	-1093	-09	9
36.78	31.68	-1083	-08	8
32.82	27.72	-1073	-07	7
28.86	23.76	-1063	-06	6
24.9	19.8	-1053	-05	5
20.94	15.84	-1043	-04	4
16.98	11.88	↓ -1033	↓ -03	3
13.02	7.92	09-50-1023	5196-02	2
B	A	EDP. NO.	ENG. NO.	極致 NO. OF CKTS.

REVISED EC NO: J2009-2074 DRWN: CARIZONO CHKD: T. HARUYAMA APPR: NUKITA	DESCRIPTION	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 4:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
		10 UNDER	± 0.2	DRAWN BY M. FUJIKURA	DATE 1992/09/07	TITLE SPOX 7.92/3.96 REC HSG		
		10 OVER 30 UNDER	± 0.25	CHECKED BY H. HIRAMOTO	DATE 1992/09/08			
		30 OVER	± 0.3	APPROVED BY M. FUKUSHIMA	DATE 1992/09/08			
		ANGULAR ±3 °		MATERIAL NO.		DOCUMENT NO.		
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE A3		SEE TABLE SD-5196-001		1 OF 1	
	REV K	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

材料
MATERIAL
ナイロン66, UL94V-2
色: オフホワイト
NYLON66, UL94V-2
COLOR : OFFWHITE