







REVISIONS									
LOC	DIST	P	F	ZONE	LTR	DESCRIPTION		DATE	APPD
CM	53					AC	085-12 8-19 PER EC 0730-0137-96	7-2-97	JH R5




1. MATES WITH APPROPRIATE UNIVERSAL MATE-N-LOK™ PLUG.
 2. RECOMMENDED PANEL THICKNESS 0.76 - 2.29.
 3. PANEL MUST BE PUNCHED SO THAT THE HOUSING ENTERS THE PANEL IN THE SAME DIRECTION AS THE PUNCH.
- △ 4 OPTIONAL FOR KEYING HOUSING IN PANEL.
- △ 5 CIRCUIT NUMBER 1 LOCATION.
- △ 6 DIMENSION INDICATED IS AS MOLDED. ADDITIONAL GROWTH DUE TO SUBSEQUENT MOISTURE ABSORPTION MAY OCCUR.
- △ 7 SIX RIBS EQUALLY SPACED, NO SPECIFIC ORIENTATION.



DETAIL A
OPTIONAL CONSTRUCTION



RECOMMENDED PANEL CUT OUT



3-DIMENSIONAL MODEL
NTS

6.99	.275	33.40	1.315
4.45	.175	33.02	1.300
2.79	.110	27.43	1.080
2.54	.100	26.16	1.030
2.29	.090	25.91	1.020
0.76	.030	20.32	.800
0.38	.015	12.19	.480
0.25	.010	8.89	.350
0.13	.005	8.13	.320
MM	IN	MM	IN

CONVERSION TABLE

METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DO NOT SCALE PRINT.
UNLESS SPECIFIED
DIMENSIONS IN mm [INCHES]
TOLERANCES ON:
2 PLC DEC ± 0.13
3 PLC DEC ± -
ANGLES ± 1°0'

MATERIAL
NYLON, UL 94V-2

FINISH
-

DR 5-28-92 K. WHITAKER	NAME	CAP, 15 CIRCUIT, UNIVERSAL MATE-N-LOK™
CHK 5-28-92 R. SWING		
APPD 5-28-92 D. SELF		
APPD 5-28-92 D. SELF		
PRODUCT SPEC -	SIZE D	CAGE CODE 00779
APPLICATION SPEC -		
WEIGHT -		

AMP Incorporated
Harrisburg, PA 17105-3608

DRAWING NO C-480711		
SCALE 4:1	SHEET 1 OF 2	

CUSTOMER DRAWING

LOC		DIST		P	F	REVISIONS					
CM		53				ZONE	LTR	DESCRIPTION	DATE	APPD	
							AC	SEE SHEET 1	-	-	