

Label - EML (15X6) R YE - 0819288

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)




Label, Roll, yellow, Unlabeled, Can be labeled with: THERMOMARK ROLL, THERMOMARK X, THERMOMARK S1.1, Mounting type: Adhesive, Lettering field: 15 x 6 mm

Illustration shows product version
EML (20X8)R YE

Why buy this product

- A wide range of marker sizes and colors are available for custom designs
- If high-quality ink ribbons are used, the labeling is resistant to solvents and suitable for use even under harsh industrial conditions
- Precise printing quality and good adhesive properties
- The EML ... materials are UL-listed
- The special packaging protects rolls that have already been started from the dirt found in industrial environments
- The EML ... self-adhesive device markers have been specifically developed for marking various types of operating equipment in control, system, and control cabinet engineering

Key commercial data

Packing unit	1 pc
GTIN	 4 046356 144209
Weight per Piece (excluding packing)	153.4 g
Custom tariff number	39199000
Country of origin	Germany

Technical data

Dimensions

Length (b)	15 mm
Width (a)	6 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	> 5 °C
Recommended storage conditions	21 °C / 50% relative humidity. Storage in poly bags is recommended prior to processing.

General

Color	yellow
Components	free from silicone and halogen

Label - EML (15X6) R YE - 0819288

Technical data

General

Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	2500
Number of individual labels per row	5
RoHS compliant	Yes
Adhesive	Acrylic
Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
	5146723 THERMOMARK ROLL X1
	5146231 THERMOMARK X1.2
	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	Following DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	DIN EN 61010-1 (VDE 0411-1):2011-07
Result	Test passed
Foil strength	55 µm
Adhesive strength	20 µm

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27141137

Label - EML (15X6) R YE - 0819288

Classifications

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410

Approvals

Approvals

Approvals

UL Recognized

Ex Approvals

Approvals submitted

Approval details



Accessories

Accessories

Ink ribbon

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black

Label - EML (15X6) R YE - 0819288

Accessories

© Phoenix Contact 2013 - all rights reserved
<http://www.phoenixcontact.com>