



4" peripheral turbine submersible pump series IDEA2 PERFORMANCE CURVES AND DATA

DIMENSIONS AND WEIGHTS			
	LENGTH mm	WEIGHT Kg	Pump Diam
IDEA2 75	355	8,0	95 mm
IDEA2 100	385	9,3	95 mm



HYDRAULIC PERFORMANCES								
CAPACITY Lt/min	7	12	16	20	24	28	35	42
CAPACITY m3/h	0,4	0,7	1	1,2	1,4	1,7	2,1	2,5
TOTAL MANOMETRIC HEAD m.w.c.								
IDEA2 75	45	40	36	32	28	24	16	8
IDEA2 100	55	50	45	40	35	30	20	10

SINGLE PAHSE	P1	Rated	CAP	TRIFASE	P1	Rated
230V-50HZ	Watt	Amp	uF	400V-50HZ	Watt	Amp
IDEA2 75	900	4,3	16	IDEA2 75	1110	1,6
IDEA2 100	1150	5,5	20	IDEA2 100	1450	2,1