



ISO view



Side view

Bracket

- ▶ Forged steel plate with khaki powder coating
- ▶ Aluminum die-casting bracket with bi-level balls upon ball seats in the swivel head
- ▶ Carbon steel handle, wide back access to level
- ▶ Aluminum cushion to stand, anti-vibration function
- ▶ Ivory texture powder coating and zinc-galvanized

Wheels

- ▶ High quality MC nylon
- ▶ High abrasion resistance, shock and impact-resistant, corrosion-resistant, ivory color
- ▶ Double ball bearing

Technical Data

Wheel Diameter	90 mm
Width of Tread	55 mm
Hardness of Tread	70 Shore D
Size of Plate	100 x 100 mm
Plate Hole Centers	70 x 70 mm
Plate Hole	13 mm
Leveling Extent	15 mm
Offset	69 mm
Overall Height	132 mm
Temperature	-10 ~ +90 °C
Load Capacity / 1pcs	1,500 kg
Load Capacity / 4pcs	3,000 kg



ENGLISH

