

## T30R5M4



Article Number: 111-03041

Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Green, 1000/pkg



### Base Data

Local Order Number T30R5M4

Type T30R

Color Green (GN)

- Features and Benefits**
- Inside serrations allow for strong hold on cables and wire bundles.
  - Head design provides high tensile strength with very low insertion force.
  - Bent tail ensures a quick and simple installation.

**Product Description** HellermannTyton standard cable ties feature inside serrations providing a positive hold onto wire and cable bundles. The head design guarantees high tensile strength, as well as a low insertion force. The bent tail design allows quick and simple installations by hand. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Fixation Method (FF) None

Identification Plate Position none

Releasable Closure (Yes/No) No

Tie Closure plastic pawl

Variant Inside Serrated

Short Description Standard Cable Tie, 5.8" Long, 30lb Tensile Strength, PA66, Green, 1000/pkg

### Product Dimensions

Minimum Tensile Strength (imperial) 30.0 lbs

Minimum Tensile Strength (N) 135.0 N

Length L (imperial) 5.8 "

Length L (metric) 148.0 mm

Width W (imperial) 0.14 "

Width W (metric) 3.6 mm

Bundle Diameter min (imperial) 0.06 "

Bundle Diameter min (metric) 1.5 mm

Bundle Diameter max (imperial) 1.38 "

Bundle Diameter max (metric) 35.0 mm

### Logistics and Packaging

Quantity per bag

Package Quantity 1000

Carton Quantity 5000

Weight (Metric) 0.7 kg

### Material and Specifications

|                                      |                                      |
|--------------------------------------|--------------------------------------|
| <b>Material</b>                      | Polyamide 6.6 (PA66)                 |
| <b>Material Shortcut</b>             | PA66                                 |
| <b>US MILSPEC</b>                    | MS3367-5-5                           |
| <b>CSA Certified</b>                 | No                                   |
| <b>Flammability</b>                  | UL94 V2                              |
| <b>Halogenfree</b>                   | Yes                                  |
| <b>Operating Temperature</b>         | -40 °F to +185 °F (-40 °C to +85 °C) |
| <b>ROHS Conformity</b>               | Yes                                  |
| <b>Certification / Specification</b> | UL ZODZ2.E64139<br>MIL 53421         |
| <b>UL Listed (US and Canada)</b>     | Yes                                  |
| <b>UL Recognized (US and Canada)</b> | Yes                                  |