



Datasheet

Stock No: 811-4390

ENGLISH

RS Pro BASEC 4 Core White Unscreened 3184Y Solid PVC Power Cable H05VV-F, 2.5 mm² CSA 20 A, 300 V, 500 V



Product Details

BASEC approved H05VV-F/3184Y 4 Core Cable

A light duty cable used for domestic appliances, kitchens and offices. They are also designed for use with light portable appliances such as radios, table lamps and office equipment.

Features and Benefits

- PVC Insulation
- Flexible copper conductor - EN 60228 Class 5

Note

Cable is not suitable for outdoor use or uindustrial applications

Standards

BASEC, EN 50525-2-11, EN/IEC 60332-1-2

Flexible PVC Cable

Specifications:

Number of Cores	4
Cross Sectional Area	2.5 mm ²
Sheath Colour	White
Current Rating	20 A
Voltage Rating	300 V, 500 V
Outer Diameter	12.5mm
Sheath Material	Polyvinyl Chloride PVC
Harmonised Code	H05VV-F
Type	3184Y
Minimum Operating Temperature	-15°C
Maximum Operating Temperature	+70°C
Screened/Unscreened	Unscreened
Conductor Strand Type	Solid
Number of Strands	50
Insulation Material	PVC Type T11 to BS7655
Standards Met	BASEC
Conductor Material	Copper
Core Strands	50/0.25 mm
American Wire Gauge	13 AWG
Size of Strands	0.25 mm
Conductor Resistance	7.98 Ω/km