

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
AD	00						
			W4	REVISED PER ECO-11-008710	27APR11	HMR	JG

D

D

C




C

B

B


A

A



RECOMMENDED HOLE LAYOUT

- 1 .000100 BRIGHT TIN-LEAD OVER .000050 NICKEL.
- 2 POINT OF MEASUREMENT FOR PLATING THICKNESS.
- 3 THE NOTED DIMENSIONS APPLY AT THE INTERSECTION OF THE POST AND THE HOUSING.
- 4 ON ASSEMBLIES WITH FOUR OR MORE POSITIONS, TWO POLARIZATION SLOTS.
ON ASSEMBLIES WITH TWO OR THREE POSITIONS, ONE POLARIZATION SLOT.
- 5 .000100 BRIGHT TIN OVER .000050 NICKEL.
- 6 PRELIMINARY PART-NOT RELEASED FOR PRODUCTION.
- 7 .000100 MATTE TIN OVER .000050 NICKEL.
- 8 HIGH TEMPERATURE CONFIGURATION
- 9 STANDOFFS NOT PRESENT ON UNDERSIDE OF ASSEMBLY
- 10 SUPERSEDED BY P/N 5-103639-2.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S.SHUEY	05MAR91	 TE Connectivity					
		CHK L.CASTAGNA	27MAR93						
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME HDR ASSY, VERT, SINGLE ROW 2.54 [100] C/L 0.64 [025] SQ POST, WITH PLZN & LATCHING, AMPMODU MTE					
		APVD L.CASTAGNA						PRODUCT SPEC	
		108-25034						APPLICATION SPEC	
		114-25026						SIZE	
MATERIAL		FINISH		CAGE CODE		DRAWING NO		RESTRICTED TO	
HOUSING:		SEE TABLE		WEIGHT		A2		-	
				CUSTOMER DRAWING		SCALE		SHEET	
						4:1		1 of 2	
								REV W4	

