

**Contact**

Cables for Industrial Applications  
 Phone: 01908 250840  
 iandi.sales@nexans.com

**H03VVH2-F**

**H03VVH2-F 2x0.75 White Coil of 25 m (in Box of 20 coils)**

**Nexans ref.: 10033771**

**Country ref.: 01231626**

**EAN 13: 3170230004882**

Flexible cable, insulation and outer sheath in PVC, domestic use.

**Description**

**Application**

H03VVH2-F cables are used for light portable domestic appliances, but are not suitable for heating and cooking appliances.

**Installation**

Open air.


**Core colours**

2 cores = Brown+ Light blue

**Marking**

S.Y + USE 'harH03VVH2-F N° Usine

For more information on Bipolar extension cords 6 A, see Related information on the bottom of the page.











**Standards**

**International**

HD 21.5;IEC 60227-1;IEC 60298

**National**

NF C 32-013;NF C 32-201/5









							
Lead free Yes	Conductor flexibility Flexible class 5	Rated Voltage Uo/ U (Um) 300 / 300 V	Mechanical resistance to impacts Low	Cable flexibility Flexible	Operating temp. range -5 .. 60 °C	Weather resistance Good	Flame retardant C2, NF C 32-070

## H03VVH2-F

**H03VVH2-F 2x0.75 White Coil of 25 m (in Box of 20 coils)**
**Nexans ref.: 10033771**

### Characteristics

Construction characteristics	
Lead free	Yes
Conductor material	Bare copper
Insulation	PVC
Conductor flexibility	Flexible class 5
Sheath colour	White
Outer sheath	PVC inner filling sheath
Dimensional characteristics	
External dimensions	3.9 x 6.4 mm
Conductor cross-section	0.75 mm <sup>2</sup>
Number of cores	2
Approximate weight	32 kg/km
Electrical characteristics	
Rated Voltage U <sub>o</sub> /U (Um)	300 / 300 V
Permissible current rating in open air	6 A
Mechanical characteristics	
Mechanical resistance to impacts	Low
Cable flexibility	Flexible
Usage characteristics	
Short-circuit max. conductor temperature	150 °C
Operating temperature, range	-5 .. 60 °C
Weather resistance	Good
Flame retardant	C2, NF C 32-070
Chemical resistance	Accidental
Water proof	Accidental
Packaging	Box of 20 coils of 25 m
Minimum static operating bending radius	11.7 mm

							
Lead free Yes	Conductor flexibility Flexible class 5	Rated Voltage U <sub>o</sub> / U (Um) 300 / 300 V	Mechanical resistance to impacts Low	Cable flexibility Flexible	Operating temp. range -5 .. 60 °C	Weather resistance Good	Flame retardant C2, NF C 32-070

Generated 27/01/15 for Ben Morris - <http://www.nexans.co.uk> Page 2 / 2

All drawings, designs, specifications, plans and particulars of weights, size and dimensions contained in the technical or commercial documentation of Nexans is indicative only and shall not be binding on Nexans or be treated as constituting a representation on the part of Nexans.