

Features

Regulated Converters

- 2:1 and 4:1 Wide Input Voltage Ranges
- 1kVDC, 2kVDC & 3kVDC Isolation
- UL94V-0 Package Material
- Continuous Short Circuit Protection
- Low Noise
- No External Capacitor needed
- Efficiency to 83 %

Description

High power-density, an industrial temperature range of -40°C to +85°C and extra features like Remote-On-Off-control are just some of the characteristics of this converter, ideal for highly sophisticated industrial designs. The RS series is available with isolation of 2kV or 3kV by choosing option "/H2" or "/H3" in which case it is also ideal for medical applications which additionally require EN-60601-1 certification.

Selection Guide 5V, 12V, 24V and 48V Input Types

Part Number	Input Voltage Range (VDC)	Rated Output Voltage (VDC)	Output Current Full Load (mA)	Efficiency typ. (%)	Max Capacitive Load
SIP8					
RS-xx3.3S (H2/H3)	4.5-9, 9-18 18-36, 36-72	3.3	500	68-69 70-73	4700µF
RS-xx05S (H2/H3)	4.5-9, 9-18 18-36, 36-72	5	400	73-75 78	1000µF
RS-xx09S (H2/H3)	4.5-9, 9-18 18-36, 36-72	9	222	74-78 81	1000µF
RS-xx12S (H2/H3)	4.5-9, 9-18 18-36, 36-72	12	166	75-80 83	1000µF
RS-xx15S (H2/H3)	4.5-9, 9-18 18-36, 36-72	15	134	75-80 83	1000µF
RS-xx3.3D (H2/H3)	4.5-9, 9-18 18-36, 36-72	±3.3	±250	68-69 70-73	±2200µF
RS-xx05D (H2/H3)	4.5-9, 9-18 18-36, 36-72	±5	±200	73-75 78	±680µF
RS-xx09D (H2/H3)	4.5-9, 9-18 18-36, 36-72	±9	±111	74-78 81	±680µF
RS-xx12D (H2/H3)	4.5-9, 9-18 18-36, 36-72	±12	±83	75-80 83	±680µF
RS-xx15D (H2/H3)	4.5-9, 9-18 18-36, 36-72	±15	±67	75-80 83	±680µF
RS-xx3.3SZ (H2/H3)	9-36 18-72	3.3	500	75 75	4700µF
RS-xx05SZ (H2/H3)	9-36 18-72	5	400	80 80	1000µF
RS-xx09SZ (H2/H3)	9-36 18-72	9	222	80 80	1000µF
RS-xx12SZ (H2/H3)	9-36 18-72	12	166	83 83	1000µF
RS-xx15SZ (H2/H3)	9-36 18-72	15	134	84 84	1000µF
RS-xx3.3DZ (H2/H3)	9-36 18-72	±3.3	±250	73 73	±2200µF
RS-xx05DZ (H2/H3)	9-36 18-72	±5	±200	77 77	±680µF
RS-xx09DZ (H2/H3)	9-36 18-72	±9	±111	80 80	±680µF
RS-xx12DZ (H2/H3)	9-36 18-72	±12	±83	81 81	±680µF
RS-xx15DZ (H2/H3)	9-36 18-72	±15	±67	83 83	±680µF

No suffix is standard isolation (1kVDC) e.g., RS-0505S

*add suffix /H2 or /H3 for 2kVDC or 3kVDC isolation, e.g., RS-0505S/H2, RS-0505DZ/H3

ECONOLINE

DC/DC-Converter

with 3 year Warranty



2 Watt

SIP8 Isolated

Single & Dual

Output



EN-60950-1 Certified
EN-60601-1 Certified
(Suffix H3)

RS

2:1 Input
(RS0-S/D)

xx = 4.5-9Vin = 05

xx = 9-18Vin = 12

xx = 18-36Vin = 24

xx = 36-72Vin = 48

4:1 Input
(RS0-SZ/DZ)

xx = 9-36Vin = 24

xx = 18-72Vin = 48



Refer to Application Notes

www.recom-electronic.com

Electrical Specifications (measured at $T_A = 25^\circ\text{C}$, nominal input voltage, full load and after warm-up time unless otherwise specified)

Input Voltage Range		2:1 and 4:1		
Output Accuracy		±2% typ.		
Line Voltage Regulation		±0.5% max.		
Load Voltage Regulation		20%-100% Load	±0.5% max.	
Minimum Load		0%		
Output Ripple and Noise (20MHz limited)		50mVp-p max.		
Switching Frequency		Full Load	100kHz min. / 300kHz max.	
Efficiency at Full Load		See Selection Guide		
Quiescent Current		RS-05xxS_D	40mA typ.	
Nominal input Voltage		RS-12xxS_D	32mA typ.	
(Standard, /H2 and /H3)		RS-24xxS_D, SZ_DZ	25mA typ.	
		RS-48xxS_D, SZ_DZ	15mA typ.	
Isolation Voltage	Standard	(tested for 1 second)	1000VDC	
	/H2 Version	(rated for 1 minute)	500VAC / 60Hz	
		(tested for 1 second)	2000VDC	
/H3 Version	(rated for 1 minute)	1000VAC / 60Hz		
	(tested for 1 second)	3000VDC		
		(rated for 1 minute)	1500VAC / 60Hz	
Isolation Capacitance	Standard	2:1 Single	10pF min. / 40pF typ. / 60pF max.	
Isolation Capacitance	/H2 and /H3	2:1 Single	5pF min. / 30pF typ. / 60pF max.	
Isolation Capacitance	Standard	2:1 Dual	120pF min. / 170pF typ. / 250pF max.	
Isolation Capacitance	/H2 and /H3	2:1 Dual	5pF min. / 30pF typ. / 60pF max.	
Isolation Capacitance	Standard	4:1 Single/Dual	200pF max.	
Isolation Capacitance	/H2 and /H3	4:1 Single/Dual	30pF max	
Isolation Resistance		1GΩ min.		
Short Circuit Protection		Continuous		
Operating Temperature Range		2:1	−40°C to +85°C	
(No Derating)		4:1	−40°C to +75°C	
Storage Temperature Range		−55°C to +125°C		
Relative Humidity		95% RH		
Package Weight		4.7g		
Packing Quantity		22 pcs per Tube		
MTBF (+25°C)		} Detailed Information see Application Notes chapter "MTBF"	using MIL-HDBK 217F	1398 x 10 ³ hours
(+85°C)			using MIL-HDBK 217F	210 x 10 ³ hours


Derating-Graph (Ambient Temperature)




RS

Typical Characteristics

RS-24xx




RS-05xx types



Package Style and Pinning (mm)

8 PIN SIP Package



Notes

Note 1 Maximum capacitive load is defined as the capacitive load that will allow start up in under 1 second without damage to the converter

Certifications

EN General Safety Report: PS-R7219C1 EN60950-1:2001 + A11:2004

EN Medical Safety Report: PS071001601 EN60601-1:1990 + A11:1996

Pin 8 (NC*) This pin is used internally and must have no external connection.

Pin 5 (NC) Not connected internally.

Pin 3 (CTRL)

This pin provides an Off function which puts the converter into a low power mode. When the pin is 'high' the converter is OFF and when the pin is high 'Z' the converter is ON. There is no allowed low state for this pin.


Application Examples

TTL Remote CTRL Circuit

Control Pin Input Current: 10mA

Voltage Set Point Accuracy with external input/output capacitors refer to recommended test circuit: typ. ± 1% max. ±2%

Control Pin (CTRL) Input Current, control voltage applied via 1K resistor, output voltage must reduce to 0V: typ. 3mA max. 6mA



Voltage to be applied via a limiting resistor with a recommended value of 1K for RS-05xx; 3.3K for RS-12xx; RS-24xx and 10K for RS-48xx.

Isolated Remote CTRL Circuit

