

Service MANOSKOP® 730

Torque wrenches with tool carrier for interchangeable insert tools, with cut-out, with QuickRelease safety lock (size 5–65) dual signal, rapid adjustment (size 2–65), dual scale N m/ft.lb and N m/inch.lb. (size 5–80), long term accuracy and facility to accept insert/shell tools.

The robust steel tube completely encloses all working parts. The measuring element is only under load while force is being applied, no need for manual reset to zero. Any force applied to the tool after the "click" or applied in the opposite direction to the current function – e.g. forcible loosening of a jammed screw – does not act on the trigger mechanism and cannot cause damage to it. Reversible insert/shell tools allow anti-clockwise operation.

Easily adjustable without disassembly, e.g. using torque tester No 7707 W or calibration system No 7706. Deviation of indication $\pm 4\%$. With certificate.

Specification

Size 5

Scale Range 6-50 N·m

Scale Range 5-36 ft·lb

Scale Division 2 N·m

Scale Division 1 ft·lb

Size of Insert Tool Carrier in mm (MANOSKOP) (Inside Square)

mm

b mm 28

h mm 23

L mm 315

LF mm 288

SF mm 17,5

Weight g 805

