





LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			NI	REVISED PER ECO-11-005027			16MAY2011	RK	HMR

- 1 MATERIAL: NYLON UL94V-2 (NATURAL).
2. RECOMMENDED PANEL THICKNESS 2.29 [.090] MAX.
3. MARKING FOR UL AND CSA LOGO SHALL BE LOCATED ON ANY EXTERNAL SURFACE.
- 4 AMP LOGO AND CIRCUIT NUMBERS LOCATED IN AREA, EITHER SIDE, SIZE OPTIONAL, FROST BACKGROUND.
- 5 WALL THICKNESS TO MEASURE 0.36-0.51 [.014-.020].



METRIC

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. WHITAKER	05AUG2004	TE Connectivity	
		CHK D. COLEY	05AUG2004		
DIMENSIONS:		APVD D. COLEY	05AUG2004	NAME	
mm [INCHES]		PRODUCT SPEC		PLUG, 3 CIRCUIT, .093 COMMERCIAL PIN AND SOCKET	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		SIZE CAGE CODE DRAWING NO	
9 PLC ±"		WEIGHT		RESTRICTED TO	
1 PLC ±"		CUSTOMER DRAWING		SCALE 5:1 SHEET 1 OF 1 REV N1	
2 PLC ±"					
3 PLC ±"					
4 PLC ±"					
ANGLES ±"					
FINISH ±"					