


LOC	DIST	REVISIONS					
A1	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
WAR NR. 93 52 546-14			B	Polzahlvarianten erweitert	29JAN99	—	A.Zitz
93-52 545-11			B1	REVISED PER ECO-09-023929	20OCT09	KK	AEG
PASSEND ZU			B2	ECR-10-026307	20JAN11	KK	HMR
VERWENDET FÜR							
E 93-53546							

NICHT VERMASSTE KANTEN SIND NICHT MAßSTÄEBLICH

POLZ	L±0.5	BESTELL-NR.
—	—	—
2	5.08	966245-2
3	7.62	—
4	10.16	—
5	12.70	—
6	15.24	—
7	17.78	—
8	20.32	—
9	22.86	—
10	25.40	—
11	27.94	—
12	30.48	—
13	33.02	—
14	35.56	—
15	38.10	—
16	40.64	—
17	43.18	—
18	45.72	—
19	48.26	—
20	50.80	—
21	53.34	—
22	55.88	—
23	58.42	—
24	60.96	—
25	63.50	—
26	66.04	—
27	68.58	—
28	71.12	—
29	73.66	—
30	76.20	—
31	78.74	—
32	81.28	—
33	83.82	—
34	86.36	—
35	88.90	—
36	91.44	—
37	93.98	—
38	96.52	—
39	99.06	—
40	101.60	—
41	104.14	—
42	106.68	—
43	109.22	—
44	111.76	—
45	114.30	—
46	116.84	—
47	119.38	—
48	121.92	—
49	124.46	—
50	127.00	966245-0

KONTAKTSTIFT	Cu Sn	1
SIFTGEHÄUSE	PBTP-GV	GRÜN
BENENNUNG	WERKSTOFF	OBERFLÄCHE FARBE



- 1 STECKSEITE: IM BEREICH "F" 0.8µm GOLD ÜBER 1.27µm Ni
LÖTSEITE: MIN. 2.5µm ZINN ÜBER 1.27µm Ni
- 2 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 3 OBSOLETE

ZEICHNUNG GÜLTIG AB KW 20/93

DIMENSIONS: mm	DWN	25.03.93	MATERIAL	FINISH
	CHK	M.SCHAARSCHMIDT		
TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2 mm	APVD	—	TE Connectivity	
	PRODUCT SPEC	—		
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	—	NAME SPEZ. AMPMODU II STIFTLISTE EINREIHIG, LOW COST LINE	
	WEIGHT	—	SIZE	CAGE CODE
			DRAWING NO	RESTRICTED TO
	CUSTOMER DRAWING		A4 00779	966245
			SCALE	SHEET
			4:1	1 OF 1
				REV B2