


M 4/6.3A - 2 + 1 clamp and M 4/6.4A - 2 + 2 clamps

M 4/6.3A - 0 to 4 mm² (22 to 10 AWG),
20 Amps, 6 mm


Spacing 6 mm (.238")



Standard 6 mm block
one circuit and three clamps


M 4/6.4A... 0 to 4 mm² (22 to 10 AWG),
20 Amps, 6 mm

Spacing 6 mm (.238")



one circuit and four clamps

| | | Type | P/N | |
|----------------------------------|--|--------------------------|------------|--------|
| Standard blocks | Grey body | M 4/6.3A | 115 468.20 | |
| | Blue body | M 4/6.3A.N | 125 468.22 | |
| Terminal blocks for ground wires | Green / yellow body (without rail contact) | M 4/6.3A.PI | 165 589.24 | |
| | | Type | P/N | |
| Standard blocks | Grey body | M 4/6.4A | 115 479.23 | |
| | Blue body | M 4/6.4A.N | 125 479.25 | |
| Terminal blocks for ground wires | Green / yellow body (without rail contact) | M 4/6.4A.PI | 165 590.21 | |
| Characteristics | | DIN-VDE | UL | CSA |
| Wire size mm ² / AWG* | Solid wire | 0 - 4 | 22-12 | 12 AWG |
| | Stranded wire | 0 - 4 | AWG | max |
| Rated voltage | V AC / = DC | 750/900 Gr.C | 600 | 600 |
| Rated current | A | 35 | 20 | 25 |
| Rated wire size | mm ² / AWG | 4 mm ² | 12 AWG | 12 AWG |
| Wire stripping length | mm / inches | 9.5 mm/.37" | | |
| Recommended torque | Nm /lb.in | 0.5-0.8 Nm/4.4-7.1 lb-in | | |

| Accessories | | Type | P/N | |
|---|----------------------|--------------|---------------|------------|
|  | End stop (all rails) | BAM | th. 9.1 | 103 002.26 |
| | End section | grey FEM6.3A | Grey M 4/6.3A | 116 576.15 |



| | | | | |
|---|-----------|-------------------------|----------------------|---------------|
| | blue | FEM3A | Blue M4/6.3A.N | 126 576.17 |
| | yellow | FEM3A | Yellow M4/6.3A.PI | 103 862.20 |
| | orange | FEM6.4A | Grey M4/6.4A | 116 629.22 |
| | green | FEM4A | Blue M4/6.4A.N | 126 629.24 |
| | | FEM4A | Yellow M4/6.4A.PI | 103 863.21 |
| Circuit separator | grey | SCM6 | | 113 003.10 |
| Separator end section (block) | grey | -- | -- | -- |
| Separator end section (rail) | grey | -- | -- | -- |
| Test socket | DIA. 2 mm | AL2(1) | | 163 043.21 |
| | DIA. 3 mm | AL3(1) | | 163 261.00 |
| | DIA. 4 mm | -- | -- | -- |
| Test device | | DCJ | Yellow | 173 059.03 |
| Test plug | DIA. 2 mm | FC2 | DIA. 2 | 007 865.26 |
| Preassembled jumper bar <i>IP20 touchproof</i> | 2 poles | BJM6(1) | | 168 516.25 |
| | 3 poles | BJM6(1) | | 168 517.26 |
| | 4 poles | BJM6(1) | | 168 518.07 |
| | 5 poles | BJM6(1) | | 168 519.00 |
| | 10 poles | BJM6(1) | | 168 973.07 |
| Connector plate | | EL6 | | 173 627.21 |
| Jumper bar not preassembled Post+screw+washer | | BJS6 (1) | 20 POLES | 174 784.20 |
| | | EV6 | | 168 604.16 |
| Comb-type jumper bar | 10 poles | PC6 | | 113 548.26 |
| Isolating cover | | EIP | | 113 550.24 |
| Shielding connector | | -- | -- | -- |
| Protection label | | -- | -- | -- |
| Screw for protection label | 3 blocks | -- | -- | -- |
| | 4 blocks | -- | -- | -- |
| See markers section | | RC610 Side - RCT610 Top | | |