





Technical Specifications 30A Turnlok® Flanged Inlets



Flanged Inlet



Typical Specifications	
Manufacturer's Identification: Pass & Seymour/Legrand L530-FI	
Description: Locking Flanged Inlet, Power Supply	
Type: 2 Pole, 3 Wire Grounding	
Rating: 30A, 125V	
Configuration: NEMA L5-30P	
3rd Party Compliance: UL Listed, File Number E146159, Standard UL498, Attachment Plugs and Receptacles. Federal Specification WC596. CSA Certified, File Number LR1765, Standard CSA-C22.2 No. 42, General Use Receptacles and Attachment Plugs.	

Amps	Catalog Number	NEMA Config. No.	Amps	Catalog Number	NEMA Config. No.
30	<input type="checkbox"/> L530-FI	L5-30P	30	<input type="checkbox"/> L1530-FI	L15-30P
30	<input type="checkbox"/> L630-FI	L6-30P	30	<input type="checkbox"/> L1630-FI	L16-30P
30	<input type="checkbox"/> L730-FI	L7-30P	30	<input type="checkbox"/> L1730-FI	L17-30P
30	<input type="checkbox"/> L830-FI	L8-30P	30	<input type="checkbox"/> L1830-FI	L18-30P
30	<input type="checkbox"/> L930-FI	L9-30P	30	<input type="checkbox"/> L1930-FI	L19-30P
30	<input type="checkbox"/> L1030-FI	L10-30P	30	<input type="checkbox"/> L2030-FI	L20-30P
30	<input type="checkbox"/> L1130-FI	L11-30P	30	<input type="checkbox"/> L2130-FI	L21-30P
30	<input type="checkbox"/> L1230-FI	L12-30P	30	<input type="checkbox"/> L2230-FI	L22-30P
30	<input type="checkbox"/> L1330-FI	L13-30P	30	<input type="checkbox"/> L2330-FI	L23-30P
30	<input type="checkbox"/> L1430-FI	L14-30P			

Performance	
Electrical	
Dielectric Withstand Voltage	3000V minimum
Maximum Working Voltage	600VAC
Current Interrupting	Certified for current interrupting at full-rated current
Temperature Rise	30°C max. after 50 cycles at 150% rated current
Mechanical	
Terminal Identification	Green = Ground, "W" and White = Neutral, Brass = Hot
Terminal Accommodation	#12 AWG min. – #8 AWG max.
Product Identification	Amperage, Voltage, 3rd Party Compliance, NEMA Configuration
Environmental	
Flammability	UL94 V2
Operating Temperature	Maximum continuous +75°C, minimum -40°C without impact
Materials	
Flanged Casing	Polycarbonate
Blade Holder	Nylon
Blades	Tin-Plated Stresscon
Terminal Clamp	Brass
Terminal Screws	Brass
Ground Screws	Brass
Assembly Screws	Zinc-Plated Steel

Consult Turnlok® Section H for complete compliance listing.