



Form Type	Distribute	Version	2.0	Ref	IPC 1752A	Sectionals	Material Info	Subsectionals	D, A
Supplier Information									
Company Name	TE Connectivity	Request Document ID		Contact Name	Benfer, David W	Contact Title	Prod Compliance Engineer		
Company Unique ID	TE Connectivity	Response Date	2015-06-22	Contact Email	dave.benfer@te.com				
Contact Phone Number	717-986-3725								
Legal Statement									
Supplier Acceptance	true								
Legal Statement									
The information provided in this document is based upon reasonable inquiry of our suppliers. This information is subject to change. This information does not in any way modify existing purchase specifications or existing contractual or other agreements terms between TE Connectivity (or its affiliated companies) and its customers.									
Product									
Manufacturer Item number	1064530-1	Amount	971.0158006	Version	-	Identity			
Manufacturer Item Name	9960 1200 24	Weight Uom	mg	Mfr Site		Authority			
Date		UOM	Each						
EUroHS-0508	Product(s) meets EU RoHS requirement without any exemptions								
ChinaRoHS-0508	Product(s) is eligible for marking with the e code under China's Measures for Administration of the control of pollution by Electronic Information Products								
EUREACH-1214	REACH Candidate Substances of Very High Concern ARE NOT Yet Reviewed								
Product Disclosure									
Sub-Item/Material/Substance	Level	Name	Substance Category	Substance CAS	Substance Concentration	Quantity	Mass per Unit	UOM	Exemption
Sub-Item	1	2400 11 0154.FEMALE CONTACT				2.0	2.0000002	mg	
Material	2	Beryllium Copper				2.0	1.914182	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	0.03828364	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	1.9142E-4	mg	
Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	3.8284E-4	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.00382836	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.00382836	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.00765673	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	1.9142E-4	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.00382836	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	1.914182E-5	mg	
Substance	3	Copper	Supplier	7440-50-8	96.649	2.0	1.85004	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.00191418	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.00382836	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	9.57091E-5	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	1.0E-5	mg	
Material	2	Nickel Plate				2.0	0.054	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	1.08E-4	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	5.4E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.053838	mg	
Material	2	Gold Plate				2.0	0.0318182	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	2.0	0.03172275	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	2.0	9.54546E-5	mg	
Sub-Item	1	2400 03 0154.SSMT JACK HOUSING				2.0	53.0000001	mg	
Material	2	Beryllium Copper				2.0	52.914912	mg	
Substance	3	Beryllium	Supplier	7440-41-7	2.0	2.0	1.0583	mg	
Substance	3	Arsenic	Supplier	7440-38-2	0.01	2.0	0.00529149	mg	

Substance	3	Manganese	Supplier	7439-96-5	0.02	2.0	0.01058298	mg	
Substance	3	Cobalt	Supplier	7440-48-4	0.2	2.0	0.10583	mg	
Substance	3	Silicon	Supplier	7440-21-3	0.2	2.0	0.10583	mg	
Substance	3	Iron	Supplier	7439-89-6	0.4	2.0	0.21166	mg	
Substance	3	Antimony	Supplier	7440-36-0	0.01	2.0	0.00529149	mg	
Substance	3	Aluminum	Supplier	7429-90-5	0.2	2.0	0.10583	mg	
Substance	3	Chromium	Supplier	7440-47-3	0.0010	2.0	5.2915E-4	mg	
Substance	3	Copper	Supplier	7440-50-8	96.649	2.0	51.14173	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	0.05291491	mg	
Substance	3	Nickel	Nickel	7440-02-0	0.2	2.0	0.10583	mg	
Substance	3	Cadmium	Cadmium/Cadmium Compounds	7440-43-9	0.0050	2.0	0.00264575	mg	
Substance	3	Mercury	Mercury/Mercury Compounds	7439-97-6	5.0E-4	2.0	2.6457E-4	mg	
Material	2	Nickel Plate				2.0	0.0429295	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-1212	0.2	2.0	8.5859E-5	mg	
Substance	3	Lead	Lead/Lead Compounds	7439-92-1	0.1	2.0	4.29295E-5	mg	
Substance	3	Nickel	Nickel	7440-02-0	99.7	2.0	0.04280071	mg	
Material	2	Gold Plate				2.0	0.0421586	mg	
Substance	3	Gold	Supplier	7440-57-5	99.7	2.0	0.04203212	mg	
Substance	3	Contains No Reportable TE5081-2 Substances	Supplier	TE5081-2-0909	0.3	2.0	1.2648E-4	mg	
Sub-Item	1	2400 06 0154,DIELECTRIC				2.0	4.0	mg	
Material	2	PP				2.0	4.0	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 2-[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropyl]hydrazide	Supplier	32687-78-8	0.15	2.0	0.0060	mg	
Substance	3	Copper, [29H,31H-phthalocyaninato(2-)-.kappa.N29,.kappa.N30,.kappa.N31,.kappa.N32]-, (SP-4-1)-	Supplier	147-14-8	0.102	2.0	0.00408	mg	
Substance	3	Propanoic acid, 3,3-thiobis-, 1,1-dioctadecyl ester	Supplier	693-36-7	0.2	2.0	0.0080	mg	
Substance	3	Octadecanamide, N,N-1,2-ethanediyldis-	Supplier	110-30-5	0.22	2.0	0.0088	mg	
Substance	3	Carbon black	Supplier	1333-86-4	0.0010	2.0	4.0E-5	mg	
Substance	3	C.I. Pigment Yellow 53	Supplier	8007-18-9	0.743	2.0	0.02972	mg	
Substance	3	Antimony oxide (Sb2O3)	Supplier	1309-64-4	6.5	2.0	0.26	mg	
Substance	3	Benzenepropanoic acid, 3,5-bis(1,1-dimethylethyl)-4-hydroxy-, 1,1-[2,2-bis[[3-[3,5-bis(1,1-dimethylethyl)-4-hydroxyphenyl]-1-oxopropoxy]methyl]-1,3-propanediyl] ester	Supplier	6683-19-8	0.15	2.0	0.0060	mg	
Substance	3	1-Propene, homopolymer	Supplier	9003-07-0	78.016	2.0	3.12064	mg	
Substance	3	C.I. Pigment Blue 29	Supplier	57455-37-5	0.908	2.0	0.03632	mg	
Substance	3	Limestone	Supplier	1317-65-3	0.01	2.0	4.0E-4	mg	

Substance	3	Benzene, 1,1-(1-methylethylidene)bis[3,5-dibromo-4-(2,3-dibromopropoxy)-	Brominated Flame Retardants (other than PBBs or PBDEs)	21850-44-2	13.0	2.0	0.52	mg	
Sub-Item	1	9960 48 0154,CABLE				1.0	853.0158	mg	
Material	2	Shield				1.0	315.45811698	mg	
Substance	3	Silver	Supplier	7440-22-4	10.0	1.0	31.54581	mg	N/A
Substance	3	Copper	Supplier	7440-50-8	90.0	1.0	283.91231	mg	N/A
Material	2	Conductoe				1.0	91.22707703	mg	
Substance	3	Silver	Supplier	7440-22-4	4.672897196	1.0	4.26295	mg	N/A
Substance	3	Copper	Supplier	7440-50-8	38.31775701	1.0	34.95617	mg	N/A
Substance	3	Iron	Supplier	7439-89-6	57.00934579	1.0	52.00796	mg	N/A
Material	2	Jacket				1.0	278.37047348	mg	
Substance	3	Titanium oxide (TiO2)	Supplier	13463-67-7	33.33333333	1.0	92.79016	mg	N/A
Substance	3	C.I. Pigment Blue 28	Supplier	1345-16-0	33.33333333	1.0	92.79016	mg	N/A
Substance	3	1-Propene, 1,1,2,3,3,3-hexafluoro-, polymer with 1,1,2,2-tetrafluoroethene	Supplier	25067-11-2	33.33333333	1.0	92.79016	mg	N/A
Material	2	Insulation				1.0	167.96013251	mg	
Substance	3	Ethene, 1,1,2,2-tetrafluoro-, homopolymer	Supplier	9002-84-0	100.0	1.0	167.96013	mg	N/A