


1 WIRE RANGE: 0.12–0.9mm² (26–18 AWG).

2 INSULATION RANGE: 1.27–2.92 [.050–.115] MAX. DIA.

3 DIMENSIONS IN BRACKETS ARE IN INCHES.

△

4 PLATE INTERNALLY WITH 0.00076 [.000030] MIN GOLD IN THE LOCALIZED GOLD PLATE AREA, GOLD FLASH ON THE REMAINDER, OVER 0.00127 [.000050] MIN NICKEL UNDERPLATE.



SECTION A—A SCALE 10:1		
SECTION B—B SCALE 10:1		
SECTION C—C SCALE 10:1		
△4 GOLD STRIPE		0.20 [.008] PHOS BRZ
PRE—TIN		0.20 [.008] PHOS BRZ
FINISH		MATERIAL
		PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

mm [INCHES]

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± —

1 PLC ± —

2 PLC ± —

3 PLC ± 0.13 [.005]

4 PLC ± — ± —

ANGLES

MATERIAL

SEE TABLE

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN

K. SALMON

9-28-94

CHK

R. SWING

9-28-94

PRODUCT SPEC

—

APPLICATION SPEC

—

WEIGHT

—

CUSTOMER DRAWING

NAME

MR RECEPTACLE

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A1

00779

641294

—

SCALE

5:1

SHEET

1

OF

1

REV

E2

METRIC

TE Connectivity