




Product Datasheet

ENGLISH

POLYPROPYLENE TERMINAL BLOCKS



Specification

HOUSING: POLYPROPYLENE (PP)

INSERTS: BRASS

SCREWS: GALVANISED STEEL

TEMP.: 85°C

COLOR: WHITE OR BLACK


Standard: CE (BS EN 60998)

Feature:

SEMI-RIGID & LOW-COST

FLAME RETARDANT

ALL SCREWS ARE CAPTIVE & RAISED FOR EASY WIRING



Dimensions

| ART. NO. | SIZE | COLOUR | RATED VOLTAGE | RATED CURRENT | DIMENSIONS | | | | | | |
|----------|------------------------|--------|---------------|---------------|------------|------|-----|-----|------|----|------|
| | | | | | L | W | Φ1 | Φ2 | D | H | d |
| 7033814 | 2.5 MM ² | WHITE | 400 V | 3~24 A | 93.7 | 16 | 2.8 | 2.1 | 8 | 15 | 8.1 |
| 7033833 | | BLACK | | | 93.7 | | | | | | |
| 7033818 | 4 MM ² | WHITE | 400 V | 5~32 A | 116.5 | 20.5 | 3.3 | 3.1 | 10 | 17 | 10 |
| 7033836 | | BLACK | | | 116.5 | | | | | | |
| 7033827 | 6 MM ² | WHITE | 400 V | 10~57 A | 139.5 | 23.5 | 4.5 | 3.6 | 12 | 20 | 12 |
| 7033830 | | BLACK | | | 139.5 | | | | | | |
| 7033849 | 10 MM ² | BLACK | 400 V | 10~57 A | 130.5 | 20.7 | 4.3 | 2.8 | 11 | 16 | 11.4 |
| 7033820 | 16 MM ² | WHITE | 400 V | 30~76 A | 175.5 | 25.3 | 5.5 | 4.1 | 15 | 23 | 15 |
| 7033842 | | BLACK | | | 175.5 | | | | | | |
| 7033824 | 25 MM ² | WHITE | 500 V | 40~101 A | 228.5 | 35.2 | 7.1 | 4.1 | 19.5 | 34 | 19.5 |

CROSS SECTION: RATED FOR RIGID WIRES AND CABLES (IF FOR FLEXIBLE WIRES, IT SHOULD BE REDUCED ONE-SIZE, I.E. 6 MM² TO 4 MM² .

THE DATA OF "d" IS DISTANCE OF TWO FIXING HOLES.

Φ1 WIRE ENTRY HOLE DIAMETER

Φ2 FIXING HOLE DIAMETER