

Rubber Test lead 2Kvac/dc



Part NO: RGW-1617-2

Product Code: Rubber Test lead wire 1.0 mm²

Product Description

Reference Standard

Customer's sample spec.and the general standard

Multi-construction

Single

Cable Construction

Conductor	Tinned Copper
Cross section	1.0 mm ²
Construction(±0.003mm)	T0.15× 55
Standard Dia.	1.30
Jacket	CSP rubber
Thickness	1.35
Jacket Dia.(mm)	4.0±0.1
Color	Red: Black;

Marking


No Printing

PACKAGING

25M/ Reel

Suitable Reels/Box

Design



Electrical Characteristics


Max.Conductor DC Resistance at 20°C (Ω /Km)	<18.8
Min.Insulation DC Resistance at 20°C (MΩ *Km)	200
Rated Temperature(°C)	-30~+85
Rated Voltage (V)	2 Kv
Current Rating (amps)	10 A

Color	Product code	RS PART NO.
Red	#3722	7482018
Black	#3721	7482014

RoHS GUIDELINE

We operate according to the following standards

Control Item	Standard	Testing Method	Testing Equipment
Cadmium content (Cd)	<0.01%	EN1122	ICP-AES
Lead content (Pb)	<0.1%	EPA3050B	ICP-AES
Mercury content (Hg)	<0.1%	EPA3052	ICP-AES
Chromium (VI) content	<0.1%	EPA3060(UN-VIS)	ICP-AES
Polybrominated Biphenyls (PBB)	Forbidden	GC/MS	
Polybrominated Diphenyl Ether (PBDE)	Forbidden	GC/MC	



Revision History

A0-1

Label on Plastic bag

Product label

Rubber Test Lead

Color

25M

RoHS(2002/95/EC) Compliant

WW/YY

RS label

RS PART NO.
25M

Made in China



Color =Jacket Color

WW=Week

YY=Year

Date:	2011-11-08
Page:	1 / 1