

WBX 2/G	WBX 8
WBX 3	WBX 8/GS
WBX 3/G	WBX 16/2/G
WBX 4	WBX M2
WBX 4/GS	WBX M4

Weatherproof enclosures

- ◆ A range of moisture and dirt resistant enclosures for the convenient installation of ESP protectors and their associated CME kits.
- ◆ Enclosures have a grey base with either a see-through or grey (part number /G') lid .

Application

Use WBX enclosures when your ESP protector (s) can't be installed within the existing equipment panel or enclosure and for added protection in damp and dirty environments.

Features and benefits

- ✓ Tough plastic enclosures (except PVC WBX 2/G).
- ✓ Weatherproof - with IP resistance to dirt and water of IP56 or more.
- ✓ Clear lid enables easy visual inspection of the protectors visual status indication (WBX 3, WBX 4, WBX 8, WBX M2, WBX M4).
- ✓ Grey lid for applications not needing regular protector inspection (WBX 2/G, WBX 3/G, WBX 4/GS, WBX 8/GS and WBX 16/2/G).
- ✓ For external CCTV and other installations requiring added security the WBX 4/GS and WBX 8/GS are supplied with an opaque lid and special secure head screws (plus tool).



- ✓ Supplied complete with metal base (mounting) plate with pre-prepared mounting positions and fixing hardware for easy installation (except WBX 2/G).

- ✓ Straightforward installation instructions with every enclosure.

Installation

The protector(s), or CME kit, are mounted on the metal base plate, which in turn mounts in the enclosure.



For added security, 'G/S' versions (eg WBX 4/GS) are supplied with an opaque lid and optional secure head screws (plus tool).



If you've got . . .

1 single phase protector
 1 three phase protector
 1 ESP 415 M2
 1 ESP 415 M4
 1 CME 4 and associated protectors
 1 CME 8 and associated protectors
 1 or 2 CME 16 and associated protectors
 1 or 2 single earth stud protectors
 up to 3 single earth stud protectors
 1 double earth stud protector

. . . use this enclosure

WBX 3
WBX 4
WBX M2
WBX M4
WBX 4 or the secure WBX 4/GS
WBX 8 or the secure WBX 8/GS
WBX 16/2/G
WBX 2/G
WBX 3/G
WBX 3/G

Specification

	WBX 2/G	WBX 3 WBX 3/G	WBX 4 WBX 4/GS	WBX 8 WBX 8/GS	WBX 16/2/G	WBX M2	WBX M4
Weight - unit	0.45kg	0.5kg	0.9kg	1.3kg	6.4kg	1.9k	2.2kg
- packaged	0.5kg	0.55kg	0.95kg	1.35kg	7.6kg	2.3kg	3.0kg
Dimensions							
Length - internal	164mm	222mm	225mm	225mm	460mm	254mm	254mm
- external	170mm	230mm	235mm	235mm	474mm	280mm	280mm
Width - internal	99mm	72mm	150mm	225mm	380mm	254mm	254mm
- external	105mm	80mm	160mm	235mm	396mm	280mm	280mm
Depth - internal	67mm	79mm	100mm	100mm	120mm	115mm	165mm
- external	82mm	85mm	117mm	117mm	128mm	130mm	180mm
Fixing centres (mm)	153 x 88	210 x 60	215 x 140	215 x 215	380 x 310	210 x 210	210 x 210
IP rating	IP66	IP67	IP66	IP66	IP56	IP67	IP67

If you would like more information about Keison Products or if you have a specific product requirement either click on the Enquiry Form button below or you can contact us at our UK or USA office:

 UK Office

Keison Products,
P.O. Box 2124, Chelmsford, CM1 3UP,
England.

Tel: +44 1245 600560 **Fax:** +44 1245
600030

Email: info@keison.co.uk

 USA Office

Keison Products,
233 Rogue River Highway #425, Grants Pass,
Oregon 97527-5429, USA.

Tel: +1 541 956 9929 **Fax:** +1 541 472 1218

Email: info@keison.com

[Home Page](#)

[Translate](#)

[Products](#)

[Enquiry Form](#)

[Web Resources](#)

Copyright © Keison International plc - email info@keison.co.uk