


ÖLFLEX® 150 CY

Screened and oil-resistant multi-standard cable with H05VVC4V5-K and AWM approval
Wide application range due to multiple certifications



Good chemical resistance



Oil-resistant



Interference signals

Info

Oil-resistant according to EN 50363-4-1: TM5
Harmonised (HAR): H05VVC4V5-K and UL recognized
EMC-compliant

Application range

Plant engineering
Industrial machinery
Heating and air-conditioning systems
In EMC-sensitive environments
(electromagnetic compatibility)
Mainly used in dry, damp and wet interiors (including water-oil mixtures), but not for outdoor use
For fixed installation under medium mechanical load conditions, and applications with occasional flexing at free, non-continuously recurring movement without tensile load or compulsory guidance
Note: for the use of AWM (Appliance Wiring Material) cables in industrial machinery (USA) according to NFPA 79 Ed. 2015: please see the catalogue appendix table T29

Product Make-up

Fine-wire strand made of bare copper wires
PVC core insulation
Cores twisted in layers
PVC inner sheath, grey
Tinned-copper braiding
PVC outer sheath, high oil-resistance, grey (RAL 7001)

Norm references / Approvals

H05VVC4V5-K (EN 50525-2-51)
UL AWM Style 21098
CSA AWM I A/B II A/B
Multi-standard cables have conductor strands with nominal sizes in mm² or AWG/kcmil. The master size is mentioned in the table below, while the equivalent size of the other system can be found in the Appendix T16 of this catalogue. For this related secondary size the cross-section of the conductor mostly works out to be greater than the specified nominal value.

Product features

Flame-retardant according to IEC 60332-1-2
and UL 1581 §1061 Cable Flame Test
Oil-resistant according to EN 50363-4-1: TM5
High degree of screening
low transfer impedance
(max. 250 Ω/km at 30 MHz)

ÖLFLEX® 150 CY

Technical Data

Core identification code:	Black with white numbers acc. to VDE 0293-1
Classification:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0 Class-Description: Control cable
Conductor stranding:	Fine wire according to VDE 0295, class 5/IEC 60228 class 5
Minimum bending radius:	Occasional flexing: 20 x outer diameter Fixed installation: 6 x outer diameter
Nominal voltage:	HAR U ₀ /U: 300/500 V UL/CSA: 600 V
Test voltage:	3000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	Occasional flexing: HAR: -5°C to +70°C UL/CSA: -5°C to +90°C Fixed installation: HAR: -40°C to +70°C UL/CSA: -40°C to +90°C

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil ≤ 30 kg or ≤ 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 600 m drum or 8 x 75 m coils).

Photographs are not to scale and do not represent detailed images of the respective products.

**ÖLFLEX® 150 CY**

Part number	Number of cores and mm ² per conductor	Outer diameter (mm)	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® 150 CY				
0015602	2 X 0,75	8,5	40.0	109
0015603	3 G 0,75	8,9	51.0	125
0015604	4 G 0,75	9,6	70.0	157
0015605	5 G 0,75	10,3	77.0	180
0015607	7 G 0,75	12,3	93.0	226
0015612	12 G 0,75	14,8	155.0	325
0015702	2 X 1,0	8,8	46.4	121
0015703	3 G 1,0	9,4	76.0	145
0015704	4 G 1,0	10.0	80.0	180
0015705	5 G 1,0	11.0	95.0	203
0015707	7 G 1,0	13.0	118.0	273
0015712	12 G 1,0	15,6	195.0	425
0015802	2 X 1,5	10.0	59.2	151
0015803	3 G 1,5	10,5	84.0	159
0015804	4 G 1,5	11,4	94.8	211
0015805	5 G 1,5	12,7	122.0	241
0015807	7 G 1,5	15,1	143.0	306
0015812	12 G 1,5	17,8	254.0	480
0015903	3 G 2,5	11,9	120.0	245
0015904	4 G 2,5	13,2	170.0	295
0015905	5 G 2,5	14,7	205.0	365
0015907	7 G 2,5	17,5	241.0	480