

Antenna - RAD-ISM-2400-ANT-VAN- 3-1-MCX - 2885702

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Omnidirectional antenna with protection against vandalism, 2.4 GHz, 3 dBi gain, IP55 protection, 1.5 m cable length, MCX (male) connection, opening angle h/v 360°/85°. Appropriate mounting material is available for wall mounting.

Why buy this product

- Version with higher impact strength that is not immediately recognizable as an antenna
- Omnidirectional antennas to increase gain



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 096676
Weight per Piece (excluding packing)	169.8 g
Custom tariff number	85177011
Country of origin	Poland

Technical data

Dimensions

Width	86 mm
Height	43 mm

Ambient conditions

Degree of protection	IP55
Ambient temperature (operation)	-40 °C ... 80 °C
Ambient temperature (storage/transport)	-40 °C ... 80 °C

General

Frequency range	2.4 GHz
	2.4 GHz
Horizontal beamwidth	360 °
Vertical beamwidth	85 °
Impedance	50 Ω

Antenna - RAD-ISM-2400-ANT-VAN- 3-1-MCX - 2885702

Technical data

General

Gain	3 dBi
Wind velocity	160 km/h (Has a force of 10 N)
Connection method	MCX (male)
Material	ASA (Antenna housing)

Classifications

eCl@ss

eCl@ss 4.0	27250312
eCl@ss 4.1	27250312
eCl@ss 5.0	19070102
eCl@ss 5.1	19070102
eCl@ss 6.0	19070102
eCl@ss 7.0	19070102
eCl@ss 8.0	19070102

ETIM

ETIM 2.0	EC000416
ETIM 3.0	EC001698
ETIM 4.0	EC001698
ETIM 5.0	EC001698

UNSPSC

UNSPSC 6.01	43171611
UNSPSC 7.0901	43221706
UNSPSC 11	43171611
UNSPSC 12.01	43221706
UNSPSC 13.2	43221706

Accessories

Accessories

Mounting material

Mounting material - RAD-ANT-VAN-MKT - 2885870




Mounting material for wall mounting of OMNI omnidirectional antenna with protection against vandals

Drawings

Antenna - RAD-ISM-2400-ANT-VAN- 3-1-MCX - 2885702

Drilling diagram



Dimensioned drawing

