


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION  
 © COPYRIGHT BY TYCO ELECTRONICS CORPORATION. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
H	-	A	INITIAL RELEASE	16OCT2009	RC AH



NOTES:

- 1 ATTENUATION  $\leq 0.3$  dB, MEASURED AT 850 nm OR 1300 nm ACCORDING TO I.E.C. 61300-3-4 INSERTION METHOD B
- 2 RETURN LOSS  $\geq 20$  dB, IN MATED CONDITION AGAINST REFERENCE CONNECTOR AT 850 nm OR 1300 nm
- 3 TEST RESULT SHEET IS SUPPLIED WITH EACH INDIVIDUAL PACKED ASSEMBLY
- 4 CABLE INFORMATION:
  - CORE DIAMETER: 62.5/125  $\mu$ m
  - OUTER JACKET DIAMETER: 0.9 mm
  - OUTER JACKET COLOUR: BLUE
  - OUTER JACKET MATERIAL: LSZH

STANDARD LENGTHS ACCORDING TO CUSTOMER DRAWING 1206850	
PART NUMBER	"L" (meter)
X-2061305-Y	XY.0

Qty	Description	Item
1	TEST RESULT SHEET	-
1	SC CONNECTOR, MULTI MODE, BEIGE	2
L	FOCAB 0.9S 62.5/125, BLUE, LSZH	1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN R. COOLEN 16OCT2009	Tyco Electronics Corporation 's-Hertogenbosch, Nederland	
DIMENSIONS: mm		CHK A. HENGELMOLEN 16OCT2009	NAME FIBER OPTIC PIGTAIL 0.9S SC/PC MULTI MODE 62.5/125	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. HENGELMOLEN 16OCT2009	SIZE A2 CAGE CODE 00779 DRAWING NO C=2061305 RESTRICTED TO -	
0 PLC $\pm -$		PRODUCT SPEC -	SCALE NTS SHEET 1 of 1 REV A	
1 PLC $\pm -$		APPLICATION SPEC -	CUSTOMER DRAWING	
2 PLC $\pm -$		WEIGHT -		
3 PLC $\pm -$				
4 PLC $\pm -$				
ANGLES $\pm -$				
FINISH -				