

EP01 6H/6G

- spectrum Machine Tap
- spectrum Maschinen-Gewindebohrer
- spectrum Machinetappen
- spectrum Tarauds machine
- spectrum Machos de máquina
- spectrum Macho Máquina



NEW

2010.02



EP01 6H



- 1.1 1.2 1.3 1.4 1.5 2.1 2.2
- 1.6 2.3 3.1 3.2 3.3 3.4

M	P mm	l ₁ mm	l ₂ mm	d ₂ ∅ mm	a mm	l ₃ mm	z	↔	l ₄ mm	e-Code
2	0.40	50	6	2.8	2.1	5	3	1.6	9	EP01M2 ¹⁾
2.5	0.45	50	8	2.8	2.1	5	3	2.1	12.5	EP01M2.5 ¹⁾
3	0.50	56	9	3.5	2.7	6	3	2.5	18	EP01M3
3	0.50	56	10	2.2	1.8	4	3	2.5		EP01M3DIN376
3.5	0.60	56	11	4.0	3.0	6	3	2.9	20	EP01M3.5
4	0.70	63	12	4.5	3.4	6	3	3.3	21	EP01M4
4	0.70	63	12	2.8	2.1	5	3	3.3		EP01M4DIN376
4.5	0.75	70	13	6.0	4.9	8	3	3.8	25	EP01M4.5
5	0.80	70	13	6.0	4.9	8	3	4.2	25	EP01M5
5	0.80	70	13	3.5	2.7	6	3	4.2		EP01M5DIN376
6	1.00	80	15	6.0	4.9	8	3	5	30	EP01M6
6	1.00	80	15	4.5	3.4	6	3	5		EP01M6DIN376
7	1.00	80	15	7.0	5.5	8	3	6	30	EP01M7
8	1.25	90	18	8.0	6.2	9	3	6.8	35	EP01M8
8	1.25	90	18	6.0	4.9	8	3	6.8		EP01M8DIN376
10	1.50	100	20	10.0	8.0	11	3	8.5	39	EP01M10
10	1.50	100	20	7.0	5.5	8	3	8.5		EP01M10DIN376
12	1.75	110	23	9.0	7.0	10	3	10.3		EP01M12
14	2.00	110	25	11.0	9.0	12	3	12		EP01M14
16	2.00	110	25	12.0	9.0	12	3	14		EP01M16
18	2.50	125	30	14.0	11.0	14	4	15.5		EP01M18 ¹⁾
20	2.50	140	30	16.0	12.0	15	4	17.5		EP01M20 ¹⁾
22	2.50	140	34	18.0	14.5	17	4	19.5		EP01M22 ¹⁾
24	3.00	160	38	18.0	14.5	17	4	21		EP01M24 ¹⁾
27	3.00	160	38	20.0	16.0	19	4	24		EP01M27 ¹⁾
30	3.50	180	45	22.0	18.0	21	4	26.5		EP01M30 ¹⁾

EP01 6G



- 1.1 1.2 1.3 1.4 1.5 2.1 2.2
- 1.6 2.3 3.1 3.2 3.3 3.4

M	P mm	l ₁ mm	l ₂ mm	d ₂ ∅ mm	a mm	l ₃ mm	z	↔	l ₄ mm	e-Code
3	0.50	56	9	3.5	2.7	6	3	2.5	18	EP01M36G
4	0.70	63	12	4.5	3.4	6	3	3.3	21	EP01M46G
5	0.80	70	13	6.0	4.9	8	3	4.2	25	EP01M56G
6	1.00	80	15	6.0	4.9	8	3	5	30	EP01M66G
8	1.25	90	18	8.0	6.2	9	3	6.8	35	EP01M86G
10	1.50	100	20	10.0	8.0	11	3	8.5	39	EP01M106G
12	1.75	110	23	9.0	7.0	10	3	10.3		EP01M126G
16	2.00	110	25	12.0	9.0	12	3	14		EP01M166G
20	2.50	140	30	16.0	12.0	15	4	17.5		EP01M206G ¹⁾

¹⁾ HSCo