



Thermal transfer printer

TT430

Features and Benefits

- Medium volume single sided printing
- Print on THTT DS, TLFX DS, TDRT DS and TULT DS (Ladder Products)
- Print on THTT, TLFX, TDRT, TULT, and TCGT (Continuous Tubing)
- Print on TAGHT, TAGLF, TAGDR, TAGUL, TAGPU, Tiptags
- Print on Adhesive Labels
- Uses standard ribbons
- Barcodes: standard and 2D
- Print speed up to 125 mm/s (30mm/s recommended for Ladder Products and Tubing)
- Adjustable label sensor
- Multiple language selection
- Windows drivers: 32/64 bit for Windows XP, Windows Vista, Windows 7 and Windows 8
- Options: External Reel Holder, Cutter (S430) and Perforator (P430)



TT430 thermal transfer printer.

Print Method	Thermal Transfer
Print Head Type	300 dpi, flat type
Print Speed	up to 125 mm/s
Max. Print Width	106 mm
Label Height Max (metric)	1,000 mm
Printer Interfaces	USB 2.0, Ethernet 10/100 Base T
Supported Barcodes, Printer	Standard and 2D
Printer Memory	64 MB RAM
Dimensions W x H x D	253 mm x 189 mm x 322 mm
Weight	4 kg
Specifications	CE, FCC, UL



One Step to the Web!



TYPE	Article-No.
TT430	556-00450

Subject to technical changes.

TYPE	Description	Article-No.
S430 Cutter	Cutter for TT430	556-00452
P430 Perforator	Perforator for TT430	556-00456
TT External Reel Holder	External Reel Holder	556-00451
TT430 300dpi Printhead	Printhead for TT430	556-00453
TT430 Print Roller	Print Roller for TT430	556-00454

Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.