


Datasheet

New Japan Radio NJM4580E, Dual Op Amp, 15MHz, 8-Pin EMP

RS Stock No: 713-9893



Product Details

Low Noise Operational Amplifiers, NJR
Operational Amplifiers, New Japan Radio

General Specifications:

Mounting Type	Surface Mount
Package Type	EMP
Power Supply Type	Dual
Number of Channels per Chip	2
Pin Count	8
Typical Gain Bandwidth Product	15MHz
Typical Dual Supply Voltage	$\pm 12\text{ V}$, $\pm 15\text{ V}$, $\pm 3\text{ V}$, $\pm 5\text{ V}$, $\pm 9\text{ V}$
Typical Slew Rate	5V/ μs
Minimum Operating Temperature	-40 °C
Maximum Operating Temperature	+85 °C
Height	1.5mm
Typical Voltage Gain	110 dB
Length	5mm
Dimensions	5 x 3.9 x 1.5mm
Width	3.9mm