

Printed-circuit board connector - MSTBH 2,5/10-G - 1765027

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)

Header, Number of positions: 10, Pitch: 5 mm, Color: green, Contact surface: Tin, Assembly: Soldering

Key commercial data

Packing unit	50 pc
GTIN	 4 017918 031756
Weight per Piece (excluding packing)	9.52 g
Custom tariff number	85366990
Country of origin	Poland

Technical data

Dimensions

Pitch	5 mm
-------	------

General

Range of articles	MSTBH 2,5/..-G
Color	green
Number of positions	10

Classifications

eCl@ss

eCl@ss 4.0	272607xx
eCl@ss 4.1	27260701
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27260704
eCl@ss 7.0	27440402
eCl@ss 8.0	27440402

ETIM

ETIM 3.0	EC001121
ETIM 4.0	EC002638
ETIM 5.0	EC002638

UNSPSC

UNSPSC 6.01	30211810
UNSPSC 7.0901	39121409
UNSPSC 11	39121409

Printed-circuit board connector - MSTBH 2,5/10-G - 1765027

Classifications

UNSPSC

UNSPSC 12.01	39121409
UNSPSC 13.2	39121409

Approvals

Approvals

Approvals

CSA / UL Recognized / VDE Gutachten mit Fertigungsüberwachung / cUL Recognized / IECCEB CB Scheme / CCA / cULus Recognized


Ex Approvals


Ex Approvals


Approvals submitted

Approvals submitted

Approval details


CSA 	
Nominal current IN	10 A
Nominal voltage UN	300 V


UL Recognized 	
Nominal current IN	10 A
Nominal voltage UN	300 V

VDE Gutachten mit Fertigungsüberwachung 	
Nominal current IN	12 A
Nominal voltage UN	250 V


Printed-circuit board connector - MSTBH 2,5/10-G - 1765027

Approvals

cUL Recognized 	
Nominal current IN	10 A
Nominal voltage UN	300 V

IECEE CB Scheme 	
Nominal current IN	12 A
Nominal voltage UN	250 V

CCA	
Nominal current IN	12 A
Nominal voltage UN	250 V

cULus Recognized 	
--	--