

JP Power Supply Cord with IEC Connector C13, straight



Description

- 1 Function:
- Power Supply Cord, Protection class I
- Pin temperature 70 °C
- custom specific versions on request

Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [Mating Connectors](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Accessories](#)

Technical Data

| | | | |
|---------------------------|---|-----------|--|
| Ratings IEC | 7 A / 125 VAC; 50 Hz | Connector | C13 acc. to IEC 60320 |
| Allowable Operation Temp. | -40 °C to 70 °C | | UL 498, CSA C22.2 no. 42 (for cold conditions) pin-temperature 70 °C, 10 A, Protection Class I |
| Degree of Protection | from front side IP 40 acc. to IEC 60529 | | |
| Protection Class | Suitable for appliances with protection class I or II acc. to IEC 61140 | | |
| Material: Housing | PVC, black | | |

All Variants

| Connector | | cable | | | | Plug | | | | | Order Number |
|-----------|--------|-------------|--------------------------|------------|-------|-------|---------|----------|----------|-------|--------------|
| Type | V-Lock | Cord Type | Conductor cross section | Length [m] | Color | Type | Country | Standard | Style | Index | |
| C13 | | HVCTF3G0.75 | 3 x 0.75 mm ² | 2.0 | black | Japan | JP | JIS 8303 | straight | - | 6047.6414 |

Most Popular.

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

Packaging unit 75 Pcs

Mating Inlets/Plugs

Category / Description

[Appliance Inlet Overview complete](#)



| | |
|--|--------|
| IEC Appliance Inlet C14, Screw-on Mounting, Front or Rear Side, Solder or Quick-connect Terminal | 6100-3 |
| IEC Appliance Inlet C14, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal | 6100-4 |
| IEC Appliance Inlet C18, Screw-on Mounting, Front or Rear Side, Solder or Quick-connect Terminal | 6102-3 |
| IEC Appliance Inlet C18, Snap-in Mounting, Front Side, Solder or Quick-connect Terminal | 6102-5 |
| IEC Appliance Inlet C14, mates to Felcom | 6150 |
| Appliance Inlet further types to Cord Sets 10 A | ... |



Distribution Unit Overview complete

| | |
|---|------|
| Distribution Unit for Snap-in Mounting with 1 IEC Appliance Inlet C14 and 1 Appliance Outlet F | 0712 |
| Distribution Unit with 1 IEC Appliance Inlet C14 and 2 Appliance Outlets F, Shuttered | 4741 |
| Distribution Unit with 1 IEC Appliance Inlet C14 and 4 Appliance Outlets F | 4747 |
| Distribution Unit with 1 IEC Appliance Inlet C14 or Power Cord, 5 or 6 IEC Appliance Outlets F and Extra Components | 4740 |
| EMC Power Strip with Line Filter | FLBB |

[Distribution Unit further types to Cord Sets 10 A](#)

Plug Overview complete



| | |
|---|------|
| IEC Plug E, Cord Connector (Rewireable), Straight, max. cable Diameter 8.5 mm | 4732 |
| IEC Plug E, Cord Connector (Rewireable), Straight, max. Cable Diameter 10 mm | 4735 |
| IEC Plug E, Cord Connector (Rewireable), Straight | 9009 |
| IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 8.5 mm | 4733 |
| IEC Plug E, Cord Connector (Rewireable), Angled, max. Cable Diameter 10 mm | 4736 |

[Plug further types to Cord Sets 10 A](#)

...

Power Entry Module Overview complete



| | |
|--|------|
| IEC Appliance Inlet C14 or C18 with Line Switch 1- or 2-pole | DC11 |
| IEC Appliance Inlet C14 with Line Switch 1-pole | KEB1 |
| IEC Appliance Inlet C14 with Line Switch 2-pole | KEB2 |
| IEC Appliance Inlet C14 with Line Switch 2-pole | DC21 |
| IEC Appliance Inlet C14 with Line Switch 2-pole, Fuseholder 1- or 2-pole | DD11 |

[Power Entry Module further types to Cord Sets 10 A](#)

...

Power Entry Module with line filter Overview complete



| | |
|--|------|
| IEC Appliance Inlet C14 with Filter, Line Switch 1-pole | KFB1 |
| IEC Appliance Inlet C14 with Filter, Line Switch 2-pole | KFB2 |
| IEC Appliance Inlet C14 with Filter, Line Switch 1- or 2-pole, Front or Rear Side Mounting | DC12 |
| IEC Appliance Inlet C14 with Filter, Line Switch 1- or 2-pole, PCB Mounting | DC22 |
| IEC Appliance Inlet C14 with Filter, Fuseholder 1- or 2-pole, Line Switch 2-pole | DD12 |

[Power Entry Module with line filter further types to Cord Sets 10 A](#)

...