

## PC-CONTACT ELECTRONIC SERVICE CASE

The clearly arranged tool case for the prompt and efficient servicing of computers

6100 **BERNSTEIN** PC-CONTACT with tool set

6115 **BERNSTEIN** PC-CONTACT without tool set

### Description:

Elegant, hard-wearing case made from deep-drawn, impact-resistant, grained dark brown plastic with a continuous bronze anodised aluminium frame, dustproof and rainproof, acid-resistant, scratch-resistant and non-slip.

65 tools are clearly arranged in pockets on one swiveling and one removable tray.

The back of the panel has elastic loops to take documents, discs, pcb's, measuring instruments etc.

The lid of the case is padded with foam rubber. The split plastic tray in the bottom of the case, which is intended to take spare parts, measuring instruments and soldering equipment, is 60 mm high.

The case has a lock strip with 2 locks and is centrally lockable. It has loops at the sides for attaching a carrying strap.

Outside dimensions: 460 x 350 x 170 mm

Weight without tools: approx. 3.700 kg

Weight with tools: approx. 5.400 kg

### Tool set:

No.	Description of individual tools	No.	Description of individual tools
2-127	<b>Tin knife</b> , with plastic handle, 115 mm	4-272	<b>Cross-recess screwdriver</b> , Supadriv/Pozidriv as above, size 1
2-132	<b>Spring hook</b> , nickel-plated and insulated, 175 mm	4-281	<b>Electronics cross-recess screwdriver</b> with special black handle and swivel top, size 000, blade chrome vanadium, chrome-plated, with black tip
2-161	<b>Magnetic bar</b> with double ball- and socket joint, slewable, 215 mm	4-282	<b>Electronics cross-recess screwdriver</b> as above, size 00
2-166	<b>Contact cleaner</b> , made from glass fibre, 115 mm	4-283	<b>Electronics cross-recess screwdriver</b> as above, size 0
2-265	<b>2 Test prods</b> , red and black, extremely slim, pointed and flexible, blade made from 1 mm steel wire, 155 mm	4-284	<b>Electronics cross-recess screwdriver</b> as above, size 1
2-601	<b>IC tweezers</b> , nickel-plated, 125 mm, for gripping, inserting and removing IC's	4-335	<b>Screwdriver</b> for special screws on cabinets
2-620	<b>PLCC extractor</b> for easy removal of plug-in PLCC's	4-343 VDE	<b>Voltage tester</b> , blade 60 x 3 mm
2-275	<b>Repair mirror</b> , 21 mm Ø, with handle, 180 mm long	4-407	<b>Retaining screwdriver</b> , 110 x 4 mm
3-901-12	<b>Side cutters</b> , 120 mm, for hard wire up to 0.4 mm, for soft wire up to 1.0 mm, burnished, with orange insulation	5-107	<b>Engineer's tweezers</b> , made from steel, with bent tips, 150 mm
3-906-12	<b>End cutters</b> , 120 mm, for soft wire up to 0.8 mm, burnished, with orange insulation	5-117	<b>Engineer's tweezers</b> , straight-flat-wide, 145 mm, nickel-plated
3-932-12	<b>Flat nose pliers</b> , 120 mm, burnished, with orange insulation	5-210	<b>Needle files</b> , 6-piece set
3-933-12	<b>Snipe nose pliers</b> , 120 mm, burnished, with orange insulation	5-305	<b>Combination scissors</b> , stainless, serrated, compression spring, plastic handles, 140 mm
3-945-12	<b>Snipe nose pliers</b> , 145 mm, angular long jaws, burnished with orange insulation	6-190	<b>Socket spanner set</b> , 8 pieces, in plastic case, 1 plastic handle, 7 socket spanners 1/8", 5/32", 3/16", 7/32", 1/4", 5/16", 3/8"
4-102 S	<b>Engineer's screwdriver</b> with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, 75 x 3.5 mm	6-750	<b>Special open-end wrenches</b> , 6-piece set, nickel-plated, 3 x 3.5, 4 x 4.5, 5 x 5.5, 6 x 6.5, 7 x 8, 9 x 10 mm, material thickness 1.5 resp. 2.0 mm
4-103 S	<b>Engineer's screwdriver</b> as above, blade 100 x 4 mm	6-771	<b>Adjustable wrench</b> , jaw opening 0 - 12 mm, total length 100 mm
4-161	<b>Electronics screwdriver</b> with special handle and swivel top, blade chrome vanadium, chrome-plated, with black tip, blade 40 x 1.0 mm	6-880	<b>Set of wrench keys</b> , 8 pieces in plastic case, 1/16", 5/64", 3/32", 1/8", 5/32", 3/16", 7/32", 1/4"
4-162	<b>Electronics screwdriver</b> as above, blade 40 x 1.5 mm	6-964 L	<b>TORX screwdriver</b> with special square BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, black tip, size T 9 with hole
4-163	<b>Electronics screwdriver</b> as above, blade 40 x 2.0 mm	6-965 L	<b>TORX screwdriver</b> as above, size T 10 with hole
4-165	<b>Electronics screwdriver</b> as above, blade 50 x 3.0 mm	6-966 L	<b>TORX screwdriver</b> as above, size T 15 with hole
4-271	<b>Cross-recess screwdriver</b> , Supadriv/Pozidriv, Size 0, with special square pattern BERNSTEIN handle, blade made from chrome vanadium, chrome-plated, with black tip	7-425	<b>Dust brush</b>

### To complete the set we recommend:

8-135	<b>ERSA "Multitip" soldering iron</b> , 15 W, 220 V
8-390	<b>Desoldering pump</b> , length 195 mm, 20 mm Ø
8-407	<b>Soldering wire coil</b> , 250 g, 0.8 mm Ø
8-413	<b>SPIRIG desoldering wire</b> 1.5 mm x 1.5 m
9-325	<b>Plastic box</b> , with hinged lid and adjustable compartments, 200 x 130 x 30 mm

# PC-CONTACT 6100 ELECTRONIC SERVICE CASE

Elegant, modern tool case for the most exacting standards



The service case

for the computer technology  
with the current tool assortment