



ENGLISH

Datasheet

RS Pro DP-30 Oscilloscope Scopemeter 30MHz \pm 33V dc

RS Stock No: **729-6671**



Product Details

RS Pro oscilloscope probe provides a safe means of measuring circuits with floating potentials up to 1000 V (DC and peak AC) from ground and 1300 V (DC and peak AC) differential. It converts high voltage differential input signal to low voltage ground referenced signal for display on any oscilloscope. The output BNC is calibrated to drive a high impedance load.

Features and Benefits

- Differential probe type
- 30 MHz high sensitivity model
- \pm 33 V dc maximum common mode input voltage

**Specifications:**

Attenuation	10x, 1x, 2x
Bandwidth	30 MHz
Maximum Common Mode Input Voltage	±33 V dc
Probe Type	Differential
Rise Time	12 ns, 24 ns
Accuracy	±2%
Input Impedance	2 MΩ
Output Impedance	50 Ω
Power Consumption	0.4 W
Standards Met	CE Certified