

DR2.5/5.2L

ABB contact for United Kingdom



General Information

Extended Product Type:	DR2.5/5.2L
Product ID:	1SNA290201R1100
EAN:	3472592902012
Catalog Description:	DR2.5/5.2L Spring Terminal Blocks Grey
Long Description:	DR2.5/5.2L Spring Terminal Blocks - Feed-through - Grey,2.5mm ² RatedCrossSection, 5mm Spacing TH 15 ... 5.5 Rail

Categories

Products » Low Voltage Products and Systems » Connection Devices » Terminal Blocks » Spring Terminal Blocks

Ordering

EAN:	3472592902012
Minimum Order Quantity:	100 piece
Customs Tariff Number:	85369010

Dimensions

Product Net Width:	5 mm
Product Net Height:	33 mm
Product Net Depth:	24.5 mm
Product Net Weight:	0.004 kg

Container Information

Package Level 1 Units:	100 piece
Package Level 1 Width:	101 mm
Package Level 1 Height:	47 mm
Package Level 1 Length:	220 mm
Package Level 1 Gross Weight:	0.4 kg
Package Level 1 EAN:	3472592902012
Package Level 2 Units:	1000 piece
Package Level 2 Width:	300 mm
Package Level 2 Height:	150 mm
Package Level 2 Length:	500 mm
Package Level 2 Gross Weight:	4.35 kg
Package Level 3 Units:	48000 piece
Product Packing Type:	Box

Environmental

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

ABB's website uses cookies. By staying here you are agreeing to our use of cookies. [Learn more](#)

UL/CSA:	Spring Clamp / Rigid 1x 26-12 AWG
Flammability According to UL94:	V0

Additional Information

Color:	Grey
Connecting Capacity-Main Circuit:	Spring Clamp / Flexible 1x 0.12-2.5 mm ² Spring Clamp / Rigid 1x 0.12-4 mm ² Spring Clamp / With Insulated Ferrule 1x 0.5-1.5 mm ²
Connection Type:	Spring
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Function:	Feed-through
Gauge Type:	A2
Gauge(s) of Form:	A2
IIT Publishing Status:	Level 0 - Information enabled
Insulation Material:	Polyamide
Mounting on DIN Rail:	TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Pollution Degree:	3
Product Main Type:	DR2.5/5.2L
Product Name:	Terminal block
Rated Cross-Section:	2.5 mm ²
Rated Current (I_n):	Main Circuit 24 A
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 300 A
Rated Voltage (U_r):	800 V
Recommended Screw Driver:	3.5 mm
RoHS Date:	Z
Spacing:	5 mm
Sub-Function:	Feed-through
Wire Stripping Length:	9.5 mm

Certificates and Declarations (Document Number)

cUL Certificate:	1SND162000A0204
Declaration of Conformity - CE:	1SND225016C1007
GOST Certificate:	1SND161005A1103
RoHS Information:	1SND230488F0201

Classifications

ETIM 4.0:	EC000897 - Feed-through terminal block
ETIM 5.0:	EC000897 - Feed-through terminal block
Object Classification Code:	X

